


[Home](#) » [Catalog](#) » [Fish Tapes & Conduit Tools](#) » [Fish Tapes](#) » [Fiberglass Fish Tapes](#)

100' (30.48 m) Non-Conductive Fiberglass Fish Tape



Cat. No. 56024

Product Features

Non-conductive fish tape and eyelet tip offer added protection against shock from energized sources.

Permanent, laser etched 1' (0.3 m) increments on the tape allow you to more accurately measure the depth of conduit runs and determine the amount of tape left to pay out.

Non-conductive fiberglass fish tape for flexibility and easy navigation through conduit runs.

Non-conductive eyelet slides easily over existing wires and through multiple bends.

The lightweight, strong fiberglass tape resists harsh elements and is strength rated for up to 500 pulling pounds.

Made in the USA.

Made in the USA.

Repair kit (Cat. No. 56025) available to replace non-conductive tips.

Replacement metal eyelets (Cat. No. 56116) and spiral steel

leaders (Cat. No. 56120) available.

[BUY NOW](#)
[FIND RETAILER](#)

[Specifications](#)
[Video](#)
[Downloads](#)
[Warnings](#)

Reel Diameter: 13" (330 mm)

Tape Size: 100' (30.48 m) L x 3/16" (5 mm) W

Weight (lbs.): 3.1 lbs (1.4 kg)

[partner support](#) | [american manufacturing](#) | [klein tradesman club](#) | [warranty](#) | [contact us](#) | [mobile](#) | [klein gear](#)
