


[Home](#) » [Catalog](#) » [Sheet Metal Tools/HVAC](#) » [Tube Flaring & Swaging Tools](#)

## 2-Piece 45° Flaring Tool Set



### Cat. No. 89021

#### Product Features

Self-centering, slip-on forged steel yoke easily forms quality flares. Flares 3/16" (5 mm), 1/4" (6 mm), 5/16" (8 mm), 3/8" (10 mm), 7/16" (11 mm), 1/2" (13 mm) and 5/8" (16 mm) O.D. tubing. Converts from flares to swages with easy screw-on application. Swages 3/16" (5 mm), 1/4" (6 mm), 5/16" (8 mm), 3/8" (10 mm), 1/2" (13 mm), 5/8" (16 mm) and 3/4" (19 mm) O.D. tubing.

[BUY NOW](#)
[FIND RETAILER](#)
[Specifications](#)
[Downloads](#)
[Warnings](#)

**Dimensions:** 7" (178 mm) L x 4-13/16" (122 mm) W x 3-9/32" (83 mm) H      **Weight (lbs.):** 2.0

[partner support](#) | [american manufacturing](#) | [klein tradesman club](#) | [warranty](#) | [contact us](#) | [mobile](#) | [klein gear](#)
