



Home » Catalog » Pliers » Side-Cutting Pliers » Ironworker's Work Pliers - High-Leverage

9" (229 mm) High-Leverage Ironworker's Work Pliers



Cat. No. D2000-9ST

Product Features

- Twists and cuts soft annealed rebar tie wire.*
- Cuts ACSR, screws, nails and most hardened wire.*
- High-leverage design. Rivet is closer to the cutting edge for 46% greater cutting and gripping power than other plier designs.*
- Hook bend handle.*
- Spring-loaded action for self-opening.*
- Induction hardened cutting knives for long life.*
- Hot-riveted joint ensures smooth action and no handle wobble.*
- Heavy-duty knurled jaws.*
- Unique handle tempering helps absorb the "snap" when cutting wire.*
- Precision-hardened plier head for on-the-job toughness.*
- Plastic-dipped handles for comfort and ease of identification.*
- "Handform" handles for full gripping and cutting power.*
- Custom, US-made tool steel.*

BUY NOW

FIND RETAILER

Specifications

Downloads

Warnings

Jaw Thickness: 5/8" (16 mm)
Nose Type: Square
Handle Finish: plastic-dipped

Jaw Length: 1-19/32" (40 mm)
Handle Color: royal blue
Overall Length: 9-3/8" (238 mm)

Jaw Width: 1-1/4" (32 mm)
Knife Length: 25/32" (20 mm)
Weight (lbs.): 1.10

[partner support](#) | [american manufacturing](#) | [klein tradesman club](#) | [warranty](#) | [contact us](#) | [mobile](#) | [klein gear](#)

