



Home » Catalog » Pliers » Side-Cutting Pliers » High-Leverage Side-Cutting Pliers - Heavy-Duty Cutting

Hi-Viz Side-Cutting Pliers - High-Leverage



Cat. No. D20009NEGLW

Product Features

Glow in the dark grips to easily locate your tool in dark or low lit areas.

Grips charge in natural and artificial lighting.

Cuts ACSR, screws, nails, and most hardened wire.

High-leverage design. Rivet is closer to the cutting edge for 46% greater cutting and gripping power than other plier designs.

Sure-gripping cross-hatched knurled jaws.

NOTE: Glow time and intensity may vary if charged in low light.

Clean grips regularly to maintain glow brightness.

FIND RETAILER

Specifications

Downloads

Warnings

Jaw Length: 1-19/32"

Overall Length: 9-3/8"

Jaw Width: 1-1/2"

Knife Length: 25/32"

Jaw Thickness: 5/8"

Nose Type: New England

Weight (lbs.): 1.09

Handle Finish: dipped

Handle Color: Yellow

[partner support](#) | [american manufacturing](#) | [klein tradesman club](#) | [warranty](#) | [contact us](#) | [mobile](#) | [klein gear](#)

