



Home » Catalog » Pliers » Diagonal-Cutting Pliers » High-Leverage Diagonal-Cutting Pliers - Ironworker's

9" (229 mm) High-Leverage Diagonal-Cutting Pliers - Ironworker's



Cat. No. D248-9ST

Product Features

- Angled head design for easy work in confined spaces.*
- Hooked handle for improved grip.*
- High-leverage design. Rivet is closer to the cutting edge for 36% greater cutting power than other plier designs.*
- Short jaws and beveled cutting edges permit close cutting of wire.*
- Induction-hardened cutting knives for long life.*
- Hot-riveted joint ensures smooth action and no handle wobble.*
- Plastic-dipped handles for comfort and ease of identification.*
- Custom, US-made tool steel.*

BUY NOW

FIND RETAILER



Specifications

Downloads

Warnings

Jaw Width: 1-3/16" (30 mm)

Handle Finish: plastic-dipped

Overall Length: 9-3/16" (233 mm)

Jaw Length: 13/16" (21 mm)

Cutting Knives: standard

Weight (lbs.): .68

Jaw Thickness: 7/16" (11 mm)

Handle Color: red

[partner support](#) | [american manufacturing](#) | [klein tradesman club](#) | [warranty](#) | [contact us](#) | [mobile](#) | [klein gear](#)

