



Home » Catalog » Journeyman Series » Journeyman Side-Cutting Pliers

## Side-Cutting Pliers



### Cat. No. J20017NE

#### Product Features

*Custom U.S. steel alloy is forged, precision machined, hardened, carefully tempered and finished in the US by artisans with over 150 years of proprietary world-class manufacturing experience.*

*Journeyman tools combine the best of Klein quality and workmanship with the latest in comfort and performance.*

*Dual-material Thermoplastic Polyurethane (TPU) grips provide uncompromised performance and durability.*

*Exclusive tri-position hardening process provides strong, long-lasting pliers.*

*Induction hardened cutting knives for long life.*

*Hot riveted joint ensures smooth action and no handle wobble.*

*Hot riveted joint ensures smooth action and no handle wobble.*

*Sure-gripping cross-hatched knurled jaws.*

*Unique handle tempering helps absorb the "snap" when cutting wire.*

*Unique handle tempering helps absorb the "snap" when cutting wire.*

**BUY NOW**

**FIND RETAILER**

#### Specifications

#### Downloads

#### Warnings

**Jaw Thickness:** 1/2" (13 mm)

**Knife Length:** 5/8" (16 mm)

**Handle Finish:** Journeyman

**Nose Type:** New England

**Jaw Width:** 1-1/16" (27 mm)

**Overall Length:** 7-9/16" (192 mm)

**Jaw Length:** 1-9/32" (33 mm)

**Handle Color:** Light Blue/Black

**Weight (lbs.):** 9.7

[partner support](#) | [american manufacturing](#) | [klein tradesman club](#) | [warranty](#) | [contact us](#) | [mobile](#) | [klein gear](#)

