



Home » Catalog » Voice / Data / Video Tools & Connectors » Punchdown Tools

Punchdown Screwdriver Multi-Tool



Cat. No. VDV001-081

Product Features

Terminate and cut wire in one step with included 110/66 combination cut-type punchdown blade with precision ground cutting edge.

Non-impact wire termination.

Machine-tooled steel bits for superior strength.

Heavy-duty blade barrel provides storage for bits.

Bayonet-style (twist & lock) socket accepts most manufacturers' punchdown blades.

Cushion-Grip handle for greater torque and enhanced comfort.

Tip-Ident® for quick identification of tool.

Two Phillips screwdriver tips: #1 and #2.

Two slotted screwdriver tips: 3/16" (5 mm) and 1/4" (6 mm).

Two nut drivers: 1/4" (6 mm) and 3/8" (10 mm).

One hex key: 3/8".

6-piece counter display also available: VDV001-0816.

BUY NOW

FIND RETAILER

Specifications **Video** **Downloads** **Warnings**

Overall Length: 8" (203 mm)

Included Bits: #1 & #2 Phillips, 3/16" (5 mm) & 1/4" (6 mm) Slotted, 66/110 Terminate & Cut, 66/110 Terminate & Cut, 3/8" Hex-Key

Finish: Chrome

Color: yellow/black

Weight (oz.): 9.4 oz (266.49 g)

[partner support](#) | [american manufacturing](#) | [klein tradesman club](#) | [warranty](#) | [contact us](#) | [mobile](#) | [klein gear](#)

