

Punchdown Tools

Impact Punchdown Tools

- Terminate cable in variety of cross-connect panels, blocks and keystone jacks.
- Spring loaded for fast, low effort seating and terminating.
- Selectable (Hi/Low) impact-force settings meet industry standards.
- Rubber finger grips and boot provide greater control and enhanced comfort.
- Blade storage compartment with spring loaded locking mechanism.
- Color coded yellow on the cut side of the tool.
- Bayonet style (twist & lock) socket accepts most manufacturers' tools and blades.
- Induction-hardened high-carbon steel for durability and long life.
- Replacement blades available: 110-Blade (Cat. No. VDV427-015), 66-Blade (Cat. No. VDV427-016), 66/110 Combination Blade (Cat. No. VDV427-017), Reach Extension (Cat. No. VDV427-018).



VDV427-800



Twisted Pair Cable

Cat. No.	Set Contains:	Overall Length	Weight
VDV427-800		7.0" (177 mm)	5.7 oz. (162 g)

Component No.	Color	Description	Blade Configuration End 1	Blade Configuration End 2
VDV427-013	yellow/black	impact punchdown tool	-	-
VDV427-017	black	punchdown tool blade - combination 66/110 cut type	66 terminate & cut	110 terminate & cut

Cat. No.	Set Contains:	Overall Length	Weight
VDV427-805		7.1" (180 mm)	5.6 oz. (159 g)

Component No.	Color	Description	Blade Configuration End 1	Blade Configuration End 2
VDV427-013	yellow/black	impact punchdown tool	-	-
VDV427-015	black	punchdown tool blade - 110 type	110 terminate	110 terminate & cut

Punchdown Tool Blades & Accessories

- Compatible with Impact Punchdown Tool (VDV427-013), Punchdown Multi-Tool (VDV427-047) and other bayonet style (twist & lock) socket punchdown tools.
- Terminate cable in variety of cross-connect panels, blocks and keystone jacks.
- Induction-hardened high-carbon steel for durability and long life.
- Reversible blades with termination/cutting ends and termination only ends (depending on blade type).
- Precision ground cutting-edge for clean, precise wire termination (depending on blade type).
- WorkEnds™ Kit converts the Punchdown Multi-Tool chassis (VDV427-047) into a multi-bit driver. Kit includes: WorkEnds™ adapter, reach extension, and 4 driver bits (#1 and #2 Phillips and 3/16" and 1/4" Slotted) in a convenient carrier.†



VDV427-015

VDV427-016



VDV427-017



VDV427-018



VDV770-050†



Twisted Pair Cable

Cat. No.	Color	Description	Blade Configuration End 1	Blade Configuration End 2	Overall Length	Weight
VDV427-015	black	punchdown tool blade - 110 type	110 terminate	110 terminate & cut	2.1" (52 mm)	0.5 oz. (14 g)
VDV427-016	black	punchdown tool blade - 66 type	66 terminate	66 terminate & cut	2.3" (58 mm)	0.6 oz. (17 g)
VDV427-017	black	punchdown tool blade - combination 66/110 cut type	66 terminate & cut	110 terminate & cut	2.2" (56 mm)	0.6 oz. (17 g)
VDV427-018	black	punchdown tool reach extension	bayonet style male	bayonet style female	2.6" (67 mm)	1.2 oz. (34 g)
VDV770-050	-	WorkEnds™ adapter, reach extension, and 4 driver bits (#1 and #2 Phillips and 3/16" and 1/4" Slotted) in a convenient carrier†	proprietary magnetic hex	1/4" female hex	3.2" (81 mm)	1.4 oz. (40 g)

†WorkEnds™ is not compatible with VDV427-013, VDV427-800, VDV427-805.

All dimensions are in inches and (millimeters).

⚠WARNING: Read carefully and understand instructions before using this tool.	⚠WARNING: NOT insulated. Will NOT protect against electrical shock.
⚠WARNING: Always wear approved eye protection.	⚠WARNING: Never use on or near live electrical circuits.

Voice/Data/Video Tools & Connectors

