


Flashlights

Recoil™ LED Grip-It™ 90° Flashlight

- Bright, powerful 1 watt Luxeon™ Lambertion LED utilizes Recoil LED Technology™ and provides 10,000 hours of lamp life.
- 32-lumen tested light-output produces a bright LED beam.
- Recoil LED Technology™ focuses 100% of the light forward to produce a white collimated beam that's as bright as an incandescent light.
- One-hand safety on/off switch operation.
- Rugged ABS body with durable polycarbonate lens, O-ring sealed shroud.
- 90° right-angle head design.
- Stainless steel clip and ring enable hands-free operation.
- Wrist lanyard secures and suspends flashlight in close proximity.



X21



Cat. No.	Batteries Included	Overall Length	Weight (oz.)†
X21	4 AA Alkaline	7.51" (19.1 cm)	10.5

Recoil™ LED Heavy Duty Flashlight

- Bright, powerful 1 watt Luxeon™ Lambertion LED utilizes Recoil LED Technology™ and provides 10,000 hours of lamp life.
- 32-lumen tested light-output produces a bright LED beam.
- Recoil LED Technology™ focuses 100% of the light forward to produce a white collimated beam that's as bright as an incandescent light.
- 50 hours of battery life so you won't be left in the dark.
- Twist on/off activation prevents accidental switch activation.
- Rugged ABS body with durable polycarbonate lens, O-ring sealed shroud.
- Submersible to 500 feet.
- Wrist lanyard secures and suspends flashlight in close proximity.
- Spring loaded belt clip securely attaches to belts up to 2".
- Batteries NOT included.



X35



Cat. No.	Batteries	Overall Length	Weight (oz.)
X35	3 C Alkaline	8.11" (20.6 cm)	5.9

Xenon NiMH Rechargeable Spotlight

- Heavy-duty design with dual lamp modules and a rechargeable battery system in a durable enclosure that is lightest in class at 3.8 pounds.
- Primary Xenon lamp module produces a bright, powerful white beam.
- Back-up Xenon lamp module.
- 600-lumen tested light-output generates a strong beam.
- 1,000 cycle rechargeable NiMH battery provides operating range from 1.5 hours (primary) to 2.5 hours (back-up) and 4 hours (low).
- NiMH battery-pack completely recharges in 3 to 3.5 hours.
- Rugged ABS body with nylon lens.
- X44 lays flat or stands upright and the head pivots almost 180°.
- Dual mode operation: constant on and emergency strobe.
- LED indicates when power button is on even when batteries are low.
- Quick release, one hand removal from the charger base is ideal for grab 'n' go situations.
- Quick connect charger base mounts anywhere - on a wall or in a vehicle - and it includes drilling mounts.
- Quick disconnect heavy-duty strap fits comfortably on your shoulder.
- Includes 12V plug-in adapter for direct wiring for in-vehicle charging and/or installation.
- Optional 12V mobile adapter (Cat. No. 56016) keeps the X44 ready to perform.
- Replacement Xenon bulb available (Cat. No. 56017).



X44



Cat. No.	Batteries Included	Overall Length	Weight (lbs.)†
X44	6 D NiMH	9.5" (24.1 cm)	3.8

†Weight includes batteries.

WARNING: It is important that users of these products read, understand, and follow all instructions, cautions, and warnings that are attached to and/or packed with the product.

