

VOICE/DATA/VIDEO CABLE TERMINATION TOOLS

[Product Index](#) > [Voice/Data/Video Tools](#) > [Voice/Data/Video Cable Termination Tools](#) > [VDV001-081](#)

Punchdown Screwdriver Multi-Tool

- 110/66 combination cut-type punchdown blade with precision ground cutting edge.
- Two Phillips screwdriver tips: #1 and #2.
- Two slotted screwdriver tips: 3/16" and 1/4".
- Two nut drivers: 1/4" and 3/8".
- One hex key: 3/8".
- Machine-tooled steel bits for superior strength.
- Heavy-duty blade barrel provides storage for bits.
- Bayonet-style (twist & lock) socket accepts most manufacturers' punchdown blades.
- Cushion-Grip hand for greater comfort.
- Tip-Ident® for quick identification of tool.
- 6-piece counter display also available: VDV001-0816.



Pictured: VDV001-081

| Cat. No. | Blade Configuration End 1 | Blade Configuration End 2 | Overall Length | Shank Length | Weight (lbs.) |
|------------|---------------------------------|--------------------------------|----------------|------------------|---------------|
| VDV001-081 | 110 cut-type punchdown blade | 66 cut-type punchdown blade | 8" (203 mm) | 2.75" (69.85 mm) | .59 (268 g) |

All dimensions are in inches and (millimeters) except where indicated.