



2-Piece Insulated 4" (102 mm) Screwdriver Set - Round Shanks



33532-INS

Additional Features:

- Includes one 1/4" (6 mm) cabinet-tip and one #2 Phillips-tip

Cat. No.	Set Contains	Weight		
33532-INS		9.6 oz. (272 g)		
Cat. No.	Tip Type	Tip Size	Shank Length	Overall Length
602-4-INS	Cabinet Tip	1/4" (6.4 mm)	4" (101.6 mm)	8-5/16" (211.1 mm)
603-4-INS	Phillips	#2	4" (101.6 mm)	8-5/16" (211.1 mm)

9-Piece Insulated Cushion-Grip Screwdriver Set

- Features three sizes of each tip style: cabinet, keystone, and Phillips
- Highly durable, black nylon case features: nylon-zipper closure, polypropylene handles, custom-fitted tool pockets; extra pocket is provided for storage of papers or other items
- Overall dimensions: 15-1/2" W x 11" D x 2-1/2" H (394 mm x 279 mm x 64 mm)
- Replacement case (Cat. No. 33538) available



33528

Cat. No.	Set Contains	Weight		
33528		5.4 lbs. (2.45 kg)		
Cat. No.	Tip Type	Tip Size	Shank Length	Overall Length
601-4-INS	Cabinet Tip	3/16" (4.8 mm)	4" (101.6 mm)	7-3/4" (196.9 mm)
601-7-INS	Cabinet Tip	3/16" (4.8 mm)	7" (177.8 mm)	10-3/4" (273.1 mm)
612-4-INS	Cabinet Tip	1/8" (3.2 mm)	4" (101.6 mm)	7-3/4" (196.9 mm)
602-4-INS	Cabinet Tip	1/4" (6.4 mm)	4" (101.6 mm)	8-5/16" (211.1 mm)
602-7-INS	Cabinet Tip	5/16" (7.9 mm)	7" (177.8 mm)	12-3/8" (314.3 mm)
602-8-INS	Cabinet Tip	3/8" (9.5 mm)	8" (203.2 mm)	13-3/8" (339.7 mm)
6334INS	Phillips	#1	4" (101.6 mm)	7-3/4" (196.9 mm)
603-4-INS	Phillips	#2	4" (101.6 mm)	8-5/16" (211.1 mm)
6337INS	Phillips	#1	7" (177.8 mm)	12-3/8" (314.3 mm)
33538	heavy-duty polyester case			

