







Catalog No.	Description	Std. Qty.	Pkg. Weight	List Price
ELECTRICAL SPECIALTIES (Continued)				
	ECONOMY DOOR LIGHT SWITCH <i>1 1/4" wide plate; 6 amp switch. 120V AC maximum.</i>			
209 DN	Door Switch – ‘On’ when Door is Open – 50 Pack	50	20 lbs.	12.35
209 DN	Door Switch – ‘On’ when Door is Open – 100 Pack	100	40 lbs.	11.15
	<i>Call factory for larger quantity pricing.</i>			
	SPECIFICATION GRADE DOOR LIGHT SWITCH <i>1 1/4" wide plate; 10 amp switch. 120V AC maximum.</i>			
210 DN	Door Switch – ‘On’ when Door is Open	25	11 lbs.	15.10
210 SW	Switch on plate with leads	10	3 lbs.	10.05
211 DF	Door Switch – ‘Off’ when Door is Open	5	3 lbs.	16.75
211 SW	Switch on plate with leads	10	3 lbs.	11.60
	<i>Call factory for larger quantity pricing.</i>			
	214 High Voltage Push, 120 Volts, Use on 7/8" Hole	5	1/2 lb.	44.60
	CAST BODY DOOR LIGHT SWITCH <i>1 3/16" wide plate; 6 amp switch. 120V AC maximum.</i>			
217 DN	Door Switch – ‘On’ when Door is Open – 50 Pack	50	29 lbs.	12.35
217 DN	Door Switch – ‘On’ when Door is Open – 100 Pack	100	57 lbs.	11.15
	<i>50 piece minimum. Call factory for larger quantity pricing.</i>			
	CAST BODY DOOR LIGHT SWITCH <i>1 3/16" wide plate; 10 amp switch. 120V AC maximum.</i>			
218 DF	Door Switch – ‘Off’ when Door is Open	5	3 lbs.	16.75
	ELECTRIC DOOR OPENER Standard Voltage 8-16V AC, 3-6V DC			
220	Mortise Door Opener	25	20 lbs.	35.60
220 SOL	Mortise Door Opener, Solenoid type (Specify 16V AC or 24V AC/DC)	1	1 lb.	44.45
220 RS	Mortise Type, Reverse Action (normally unlocked) 24V AC/DC only	1	1 lb.	111.50
220 S	Mortise Door Opener (1/4" plate for schlage lock)	1	1 lb.	74.10
	Add for Chrome No. 220			3.40
	Add for 24V AC			4.95
	244 RB *Roller Ball Contact for Open Circuit Use	10	1/4 lb.	10.35
	245 RB *Roller Ball Contact for Closed Circuit Use	10	1/4 lb.	10.35
	246 RB *Roller Ball Contact for Make & Break Circuit	10	1/4 lb.	10.95
	*Low Voltage Only 48V AC Max.			