



Dependable Power for Any Application

Product Datasheet

120 Primary Volts - 24 Secondary Volts - 1Ø Low Voltage Lighting Transformer - Single Phase

Catalog #: T179609S



PRODUCT FEATURES

- UL listed, CSA certified
- UL Type 2 Enclosures
- Fully encapsulated core and coil
- Wall Mounted
- Black Finish UL Type 2 Enclosure
- Input Auto-Thermal reset switch
- Output circuit breaker
- Covered under Acme's 10 year limited warranty

BENEFITS

- Copper lead wires for hardwiring
- Primary and secondary overload protection
- Full fault current carrying Farady Shield
- Single and dual knockouts

UL STANDARD

UL 506

CSA STANDARD

C22.2 No 47

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

VA:	1000
Primary Voltage:	120
Secondary Voltage:	24
Frequency:	60 Hz
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

PRODUCT MEASUREMENTS

Height (In./cm):	11.93 (30.3)
Width (In./cm):	5.41 (13.7)
Depth (In./cm):	5.20 (13.2)

CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall
Knockouts (In./Cm):	Two 0.875 (2.2) signal knockouts on each side
Knockouts 2 (In./Cm):	Two dual 0.875 (2.2) and 1.125 (2.9) knockouts on bottom cover
Wiring Diagram:	V
CB Rating:	50 Amp
CB Style:	Magnetic Toggle On/Off Breaker

PACKAGING

Ship Weight (Lbs/Kg):	26 (11.8)
-----------------------	-----------

COMPLIANCES

UL Standard:	UL 506
UL Listed:	File E79947
CSA Standard:	C22.2 No 47
CSA Listed:	LR7357-32
Warranty:	Acme Electric Warranty Card
	www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf