



Dependable Power for Any Application

Product Datasheet

208/277/380 Primary Volts - 95/115 Secondary Volts - 1Ø Industrial Control Transformer - Open Core & Coil

Catalog #: TB81309



PRODUCT FEATURES

- Meets or exceeds UL, CSA, NEMA, and ANSI standards
- UL Listed and CSA Certified
- Meets NEC Article 450
- Constructed out of electrical lamination with precision wound coils
- Primary and secondary fuse kits easily adaptable
- Add suffix "F2" to catalog for factory installed 2 pole primary block
- Add suffix "F3" to catalog for factory installed 3 pole primary and secondary block
- Covered under Acme's 10 year limited warranty

BENEFITS

- Series parallel connecting links save time and costs
- Mounting plate adapts to various mounting dimensions
- Molded terminal blocks allow easy ring terminal installation
- Optional Secondary Fuse Kits available

UL STANDARD

UL 506

CSA STANDARD

C22.2 No 66

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

| | |
|-----------------------|-------------|
| VA: | 1000 |
| Primary Voltage: | 208/277/380 |
| Secondary Voltage: | 95/115 |
| Frequency: | 50/60 Hz |
| Max Temperature Rise: | 80°C |
| UL Insulation Class: | 130°C |

PRODUCT MEASUREMENTS

| | |
|------------------|-------------|
| Height (In./cm): | 5.72 (14.5) |
| Width (In./cm): | 6.75 (17.1) |
| Depth (In./cm): | 7.96 (20.2) |

CONFIGURATION

| | |
|---------------------|----------|
| Mounting Type: | Floor |
| Primary Fuse Block: | PL112705 |
| Wiring Diagram: | E |

PACKAGING

| | |
|-----------------------|-----------|
| Ship Weight (Lbs/Kg): | 31 (14.1) |
|-----------------------|-----------|

COMPLIANCES

| | |
|---------------|--|
| UL Standard: | UL 506 |
| UL Listed: | File E79947 |
| CSA Standard: | C22.2 No 66 |
| CSA Listed: | LR7357-16 |
| Warranty: | Acme Electric Warranty Card |
| | www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf |