



Representative

**Catalog Number:** CTL300-12  
**Product ID:** 7TAH007100R0100  
**UPC Number:** 78378613191  
**Status:** Active

Copper One-Hole Lug, Short Barrel, Max 35kV, 300 kcmil Wire, 1/2 Bolt Size, Tin Plated, Die Color Code White

- Made of high-conductivity seamless copper tubing. Tin plated for corrosion resistance.
- Specifically chamfered barrel for ease of installation.
- Color-coded for matching die identification.

### North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Blackburn
Type	Short Barrel Copper Lug
Special Features	Made of high-conductivity seamless copper tubing. Tin plated for corrosion resistance.
Standard	UL E9809
Cable Size	300 kcmil
Stud Size	1/2 Inch
Number Of Holes	1
Material	Copper
Color	White

### European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	Straight
Slender flange model	N
With sight-hole	N
Material	Copper
Surface protection	Tinned
Number of fixing holes	1

### Packaging

Inner Quantity	10
Inner Dimensions (inches)	3.5x3x3
Outer Quantity	100
Outer Dimensions (inches)	16.25x8x3.75
Weight Uom	17.25 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)