



Representative

Catalog Number: LCN1-12
Product ID: 7TAH007800R0043
UPC Number: 78378603278
Status: Active

Type LCN Copper Two-Hole Lug, Long Barrel, Max 35kV, Wire Size 1 Str, 1/2 Inch Bolt Hole, Tin Plated, Die Color Code Green

- Made of high-conductivity seamless copper tubing. Tin plated for corrosion resistance.
- Specifically chamfered barrel for ease of installation.
- Color-coded for matching die identification.

North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Blackburn
Type	Long Barrel Copper Lug
Special Features	Made of high-conductivity seamless copper tubing. Tin plated for corrosion resistance.
Standard	UL E9809
Cable Size	1 Str.
Stud Size	1/2 Inch
Number Of Holes	2
Material	Copper
Color	Green

European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	Straight
Slender flange model	N
With sight-hole	N
Material	Copper
Surface protection	Tinned
Number of fixing holes	2

Packaging

Inner Quantity	20
Inner Dimensions (inches)	5.5x4x3
Outer Quantity	200
Outer Dimensions (inches)	5x4.5x3
Weight Uom	12 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com