

Selective Call Intercom 4-Location Kit, White

IC5400-WH



features & benefits

The Selective Call Intercom System combines innovative technology with elegant design. This four-room kit enables broadcast or room-to-room communication, and allows up to three simultaneous, private conversations. Based on the innovation you'd expect from On-Q, installation is simple and efficient, with unit auto-discovery and a convenient RJ45 connection.

Kit Includes:

- 1 [IC5001](#) Selective Call Intercom 8-Location Distribution Module.
- 4 [IC5000-WH](#) Selective Call Intercom Room Unit.
- 1 PW1030 24VDC 30W Power Supply.

specifications

General Info

Cable Type: Min Rating is Cat5 UTP, 4 pair solid conductors (24AWG) 100ohm 100Mhz General Purpose (CM) UL listed (325 feet max per run)

Color: White

Connection Type: Solid Conductor RJ45

Type: Kit

Listing Agencies/Third Party Information

UN SPS C: 43221525

Technical Information

Humidity: 90% Relative Humidity (Non-Condensing)

LCD Color Depth U S: 65K

LCD Size Metric: 27mm X 29mm

LCD Size U S: 1.1 in X 1.1 in

Operating Temperature Celsius: 0°C to 55°C

Operating Temperature Fahrenheit: 32°F to 131°F