
19-INCH 2U HINGED WALL MOUNT BRACKET

AC1902 | [On-Q](#)



FEATURES & BENEFITS

This hinged wall mount bracket is 19 inches wide by 2 rack mount spaces high and comes with 2 switch extenders to support mounting of active data networking products.



- Mounts any panel sized at 2 rack mount spaces high or less
- Includes two 4-inch switch extenders to support mounting of active data products
- Unique design supports mounting in corner of room
- Stack multiple brackets to support more products

SPECIFICATIONS

GENERAL INFO

Color: Black
Finish: Black painted
Special Features: Steel Rackmount Bracket

ASSEMBLY/INSTALLATION INFORMATION

Mounting Points: 8 slotted, 12 round mounting holes

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

cULus: Yes
cUL Standard: Yes
UN SPSC: 31162307

DIMENSIONS

Height (US): 3.75"
Length (US): 20"

Width (US): 7.65"

Hole Size: 8 x 10mm, 12 x 5.5mm

TECHNICAL INFORMATION

Material: Cold Rolled Steel, 1.5mm thick

Mounting: 8 x 10mm slotted bracket mounting holes, 12 x 5.5mm component mounting holes

Supported Standards: cULus

Equipment Type: Network Structured Wiring

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA