

Cat 6 EZ-RJ45 Connector

AC2006



features & benefits

Our Cat 6 EZ-RJ45 Connector makes it easy to quickly and efficiently terminate wires of any length. Large cable openings reduce the distance between the wires and contacts, creating optimal performance and reliable connections every time. Available in packs of 25.

specifications

General Info

Cable Type: For solid or stranded conductors
Category Performance Application: Cat6+
Color: Clear
Number Of Ports: 1
Pair Count: 4
Performance Category: Cat6
quantity: sold in Packs of 25
Termination: Insulation displacement
Typical Applications: Bulk wire termination for data applications

Listing Agencies/Third Party Information

cU Rus: Yes
FCC Standard: Yes

Dimensions

Cable Diameter Range: Conductors with an O.D. Range of 0.037" to 0.042"

Depth U S: 0.885

Height U S: 0.312

Primary Package Weight U S: 0.1 Lbs

Product Weight U S: 0.004 Lbs

Width U S: 0.46

Technical Information

Flammability Rating: 94-V0

Humidity: Max 93% non-condensing

Material: High impact polycarbonate

Ohm Value: Contact Resistance 10 milliohms max

Operating Temperature Celsius: minus 40 to +85

Product Fits Into: RJ45 Jacks