

vYXVkaW8tdmlkZW8vc3BIYWtlcnMuYXNweGQWAmYPFglAAUIU3BIYWtlcnNkAgMPDxYCHwQFGi9hdWRpby12aWRlby9zcGVha2Vycy5hc3B4ZBYCZg8W



designed to be better.

Search

Medium Base Lampholder

10045

Medium base, porcelain, keyless, single circuit with screw terminals, aluminum screw shell with set. White.

Submit Query

Where to buy

Submit Query

0

Email Print



Representative image shown.

- SPECIFICATIONS

features & benefits

- Quality Materials.
- Durability.
- Time-tested design.

specifications

General Info

- Type: Incandescent Medium Base Lampholder

Listing Agencies/Third Party Information

- CSA Listing Info: Yes
- CUL Listing No: No
- cU Lus: No
- cU Rus: No
- Federal Spec: No
- UL Listing No: Yes
- U N SPS C: 39111803
- U R: No

Dimensions

- Diameter U S: 1.40"
- Height Metric: 2.00"
- Weight: 0.18236
- Width U S: 1.625
- Height: 3

Technical Information

- Volts: 250V
- Volts A C: 250
- Watts: 660

Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No