

VyY2lhbC1hdi9jYWJsZS10cmF5LXdpcmUtbWVzaC5hc3B4Ij48aW1nIHJlcGxhY2U9ImRzcmMilGRzcmM9Ii9+L21lZGlhLzAzNkQ4Qjk0OTREODQ3RUQ5Qjky



designed to be better.

Search

# Panel TVSS Unit, Medium-Duty

1224SM

120/240 VAC, 3 wire and ground, Single Phase Medium-Duty TVSS Panel Unit

Submit Query

Where to buy

Submit Query

Like 0

Tweet 0

0



## product gallery

Representative images shown.

- SPECIFICATIONS
- RESOURCES

## features & benefits

- Meets UL Standard for Safety for Surge Protection Devices, UL1449 3rd Edition (effective September 29, 2009).

- P&S Panel TVSS Units meet the newest standard, bringing stronger protection to virtually any residential, commercial, or industrial application - and bringing homeowners and business management new peace of mind.
- NEMA 12 enclosure provides for indoor use protection against dust, dirt and non-corrosive liquids.
- LED visual indicators provide a method for determining the status of the surge suppression components.
- For Max Surge Capability and AIC Ratings please consult the supporting document 'Panel TVSS Units' under the 'Resources' tab.

### Top 5 Resources

-  [Surge Protective Panels, SF1307R1 \(Cutsheet\)](#)
-  [Commercial & Industrial Products \(Brochure\)](#)

### specifications

#### General Info

- Type: Single Phase
- Duty: Medium Duty
- Number Of Wires: 3
- Special Features: Isolated Ground, Audible Alarm with LED Monitor

#### Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: Yes
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: Yes
- U N SPS C: 39121406
- U R: No

#### Dimensions

- Depth (U S): 3"
- Height U S: 6"
- Width U S: 4"

#### Technical Information

- Volts: 120/240 VAC
- Volts A C: 120/240

#### Buy American Act Compliance


- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant



### resources BROCHURE

-  [Commercial & Industrial ProductsPDF \(3.52mb\)](#)

### CUTSHEET

-  [Surge Protective Panels, SF1307R1PDF \(308.85kb\)](#)