

YXlGU3VwcG9ydGQCAw8PFgJfBAUpL3dpcmUtY2FibGUtbWfuYWdlbWVudC9zb2xhci1zdXBwb3J0LmFzcHhkFgJmDxYCHwAFeTxbpWcgcmVwbGFjZT0iZl-



designed to be better.

Search

# Manual Controller, Momentary Contact Either Direction Three Position, Center Off, Ivory

1250I

Single Pole, Double Throw Manual Momentary Control Switch, 15 amps, 120/277 volts, Ivory.

Submit Query

Where to buy



Representative image shown.

## AVAILABLE OPTIONS



Manual Controller



Manual Controller



Manual Controller



Manual Controller




## Manual Controller

- SPECIFICATIONS
- RESOURCES

### features & benefits

- Oversize silver alloy contacts for long life and better heat dissipation.
- Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.
- Fiber terminal insulation barriers standard.
- Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.
- Bodies, covers, and toggles molded of durable nylon.
- Single Pole-Double Throw and Double Pole-Double Throw.
- Locking Switches supplied with one 1498-NT key.
- Normally open.

### Top 5 Resources

-  Commercial & Industrial Products (Brochure)

### specifications

#### General Info

- Color: Ivory
- Type: Momentary Contact
- Number Of Poles: 1
- Special Features: Three Position

#### Listing Agencies/Third Party Information

- CSA Listing Info: Yes
- CUL Listing No: No
- cU Lus: No
- cU Rus: No
- Federal Spec: No
- UL Listing No: Yes
- U N SPS C: 39121507
- U R: No

#### Dimensions

- Depth (U S): 1.469"
- Height U S: 3.281"
- Weight: 0.26024
- Width U S: 1.5"

#### Technical Information

- Amps: 15 Amp
- Volts: 120/277VAC
- Volts A C: 120/277

#### Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant



#### resources

##### BROCHURE

-  Commercial & Industrial ProductsPDF (3.52mb)