



designed to be better.

Manual Controller

1251W

Single Pole, Double Throw Manual Control Switch, 20 amps, 120/277 volts, White.

Where to buy

0



Representative image shown.

AVAILABLE OPTIONS






- SPECIFICATIONS
- RESOURCES

features & benefits

Oversize silver alloy contacts for long life and better heat dissipation. Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors. Fiber terminal insulation barriers standard. Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures. Bodies, covers, and toggles molded of durable nylon. Single Pole-Double Throw and Double Pole-Double Throw. Locking Switches supplied with one 1498-NT key. Normally open.

Top 5 Resources

-  Commercial & Industrial Products (Brochure)

specifications

General Info

- Color: White
- Type: Momentary Contact
- Number Of Poles: 1
- Special Features: Three Position

Listing Agencies/Third Party Information

- CSA Listing Info: Yes
- CUL Listing No: No
- cU Lus: No
- cU Rus: No
- Federal Spec: No
- UL Listing No: Yes
- U N SPS C: 39121507
- U R: No

Dimensions

- Depth (U S): 1.469"
- Height U S: 3.281"
- Weight: 0.0288
- Width U S: 1.5"

Technical Information

- Amps: 20 Amp
- Volts: 120/277VAC
- Volts A C: 120/277

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



resources BROCHURE

 [Commercial & Industrial ProductsPDF \(3.52mb\)](#)