

Electrical Accessories Fluorescent Lampholders



Fluorescent Lampholders						
Catalog Number	Rating	Description	Color	UL	CSA	
3901W	660W 600V	Medium bi-pin, screw terminals.	White	•	•	
3911W	660W 600V	Medium bi-pin, pressure lock terminals, includes starter base.	White	•	•	
464	660W 600V	Pedestal type, recessed, contact, plunger, with floor terminal screw cover (for 800 & 1500MA T-12 lamps).	White	•	•	
465	660W 600V	Pedestal type, recessed, fixed, quick wire terminals (for 800 & 1500MA T-12 lamps).	White	•	•	
466	660W 1000V	Pedestal type, recessed, plunger, quick wire terminals (for all sizes of lamps T-12, T-8, and T-6).	White	•		
467	660W 600V	Pedestal type, recessed, fixed, quick wire terminals (for all sizes of lamps T-12, T-8, and T-6).	White	•		
623	660W 600V	Snap-in, high output with plunger.	White	•	•	
2536	660W 1000V	Slimline, for single pin lamps, shallow base, slide plunger, push in terminal.	White	•	•	
2537	660W 600V	Slimline, for single pin lamps, shallow base, slide fixed, 2 push in terminals.	White	•	•	
13053UN	660W 660V	Slide-on, short, for medium bi-pin lamps with captive nut, 4 quick wire terminals.	White	•		
13057UN	660W 600V	Slide-on, for medium bi-pin with captive nut, 4 quick wire terminals.	White	•	•	