

VkaWEvMDRBNEExQzc0NjJFNDUxOUe4NEyzNzkzMzM2OEZBODUuYXNoeClgYWx0PSJXYWxsIEJveGVzliB3aWR0aD0iMjE4IiBoZWlnaHQ9IjExMilgLz4E



designed to be better.

Search

Tamper-Resistant Display Receptacle 15A/125V W/Brass Plate

1542TRDR

Tamper-Resistant Display Receptacle, 15amp 125volt With Brass Plate and plug. Brown.

Submit Query

Where to buy

Submit Query

Like 0

Tweet 0

0

Email Print





product gallery



Representative images shown.

- SPECIFICATIONS
- RESOURCES

features & benefits

- Dual mechanical shutter system to help prevent insertions of foreign objects.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- .032 inch thick brass triple-wipe power contacts for lasting retention.
- Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuitwiring.
- Backed-out tri-drive steel terminal screws. Side wire capability.

Top 5 Resources

-  [Floor Boxes \(Brochure\)](#)
-  [Tamper-Resistant Floor Box Assembly \(Installation Instructions\)](#)

specifications

General Info

- Product Series: Slater
- Component Type: Display, Receptacle

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: No
- U N SPS C: 39121308
- U R: No

Dimensions

- Depth (U S): 1.825"
- Diameter U S: 5.75
- Length: 4.500"
- Width U S: 2.750"

Technical Information

- Amps: 15 Amp
- Material: Brass
- Volts A C: 125
- Floor Type: Wood

Buy American Act Compliance

- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant




resources

BROCHURE

-  [Floor BoxesPDF \(925.15kb\)](#)

INSTALLATION INSTRUCTIONS

-  [Tamper-Resistant Floor Box AssemblyPDF \(96.89kb\)](#)