



designed to be better.

Search

# 15 Amp In-Line Portable GFCI, Manual Reset

1594TC2M

Portable Ground Fault Circuit Interrupter, 15amp 125volt, 2' Tri-Cord Connector, Manual Reset

Where to buy

Like



•



•



•



## product gallery

Representative images shown.

- SPECIFICATIONS
- RESOURCES

## features & benefits

- Durable polycarbonate case withstands hard use.
- In-line has bright, green power indicator light that is on when power is available and is visible from both sides of the GFCI.
- Open neutral protection.
- Optional Turnlok plugs and connectors prevent accidental disconnection.
- Optional tri-cord connector handles up to three loads.

## Top 5 Resources



Portable GFCI (Brochure)



Portable Ground Fault Circuit Interrupter (GFCI), Auto & Manual Reset 1594/2094 -PC2,PC6,TL2,TC2 (Installation Instructions)

## specifications

### General Info

- Type: In-Line Portable GCI, Manual Reset

## Listing Agencies/Third Party Information

- cU Lus: Yes
- Federal Spec: No
- UL Listing No: UL943, UL498
- UL Standard: Yes
- U N SPS C: 39121614

## Dimensions

- Length: 26.75"

## Technical Information

- Amps: 15 Amp
- Volts: 125
- Volts A C: 125

## Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No
- 

## resources BROCHURE

 Portable GFCIPDF (753.74kb)

## INSTALLATION INSTRUCTIONS

 Portable Ground Fault Circuit Interrupter (GFCI), Auto & Manual Reset 1594/2094 -PC2,PC6,TL2,TC2PDF (65.54kb)