




designed to be better.

 Search

TradeMaster® & Specification Grade GFCI Receptacle, Ivory

1595I

TradeMaster/Spec Grade GFCI Receptacle in ivory has SafeLock™ Protection such if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected. It prevents the line-load reversal miswire with no power to the face or downstream receptacles if wired incorrectly. It is made with high-impact-resistant thermoplastic construction. The mounting screws are shipped captive in the device and wall plate for easier installation. 10kA SCCR, 15A 125VAC.

Submit Query

Where to buy

Submit Query

Like

Tweet

 
Email Print





product gallery

Representative images shown.

AVAILABLE OPTIONS

TradeMaster® Spec Grade 15 Amp Duplex GFCI, White

TradeMaster® & Specification Grade GFCI Receptacle, Brown

TradeMaster® & Specification Grade GFCI Receptacle, Black

TradeMaster® & Specification Grade GFCI Receptacle, Gray

TradeMaster® & Specification Grade GFCI Receptacle, Light Almond


TradeMaster® & Specification Grade GFCI Receptacle, Red




- SPECIFICATIONS
- RESOURCES

features & benefits

- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.
- GFCIs with Auto-Ground assure a positive ground to metal box.

Top 5 Resources

-  [GFCI Test & Protect \(Brochure\)](#)
-  [GFCI Receptacles \(Brochure\)](#)

-  GFCI Receptacle (Installation Instructions)
-  Instalación y prueba de un tomacorriente GFCI (Installation Instructions)
-  Installation et test d'une prise DDFT (Installation Instructions)

specifications

General Info

- Color: Ivory
- Product Series: TradeMaster
- Type: GFCI Receptacle
- Style: Decorator

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No.42 & 144
- CSA Standard: Yes
- cU Lus: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121614

Dimensions

- Depth (U S): 0.98"
- Height U S: 4.2"
- Width U S: 1.72"

Technical Information



- Amps: 15 Amp
- Volts: 125
- Volts A C: 125
- Grade Type: Specification

Buy American Act Compliance


- Country of Origin: CHINA
- Buy American Act Status: No
-

resources




BROCHURE

-  GFCI Test & ProtectPDF (494.1kb)
-  GFCI ReceptaclesPDF (1.19mb)

CUTSHEET

-  Spec Grade GFCIs, SF1101R4PDF (394.6kb)

INSTALLATION INSTRUCTIONS

-  [GFCI ReceptaclePDF \(109.09kb\)](#)
-  [Instalación y prueba de un tomacorriente GFCIPDF \(639.9kb\)](#)
-  [Installation et test d'une prise DDFTPDF \(208.23kb\)](#)