



designed to be better.

Search

Decorator Combination Tamper-Resistant Nightlight/GFCI, Ivory

1595NTLTRICC4

Deco Combo Tamper-Resistant/Nightlight GFCI, 10kA SCCR, 15A 125VAC, Ivory

Where to buy

Like





product gallery

Representative images shown.

AVAILABLE OPTIONS








- SPECIFICATIONS
- RESOURCES

features & benefits

- Stylish rounded corners match Signature wall plates and devices.
- Sealed nightlight with high impact-resistant Lexan® lens prevents tampering.
- Nightlight uses cooler LED illumination.
- Energy-efficient LED has average 20-year life expectancy, eliminating bulb replacement.
- Photocell turns nightlight ON in dark, OFF in daylight.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Zinc-plated steel mounting strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Tri-drive screws.

Top 5 Resources

-  [Decorator Combination Devices \(Brochure\)](#)
-  [Better Living Upgrades \(Brochure\)](#)
-  [GFCI Receptacles \(Brochure\)](#)
-  [Tamper-Resistant Receptacles \(Brochure\)](#)
-  [Commercial & Industrial Products \(Brochure\)](#)

specifications

General Info

- Color: Ivory
- Type: Combo Nightlight/GFCI
- Special Features: Tamper-Resistant
- Style: Decorator

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No.42 & 144
- CSA Standard: Yes
- cULus: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121704

Dimensions

- Depth (U S): 1.13"
- Height U S: 4.2"
- Width U S: 1.72"






Technical Information

- Amps: 15 Amp
- Volts: 125
- Volts A C: 125


Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No
-




resources BROCHURE

-  Decorator Combination DevicesPDF (526.77kb)
-  Better Living UpgradesPDF (1.2mb)
-  GFCI ReceptaclesPDF (1.19mb)
-  Tamper-Resistant ReceptaclesPDF (791.69kb)
-  Commercial & Industrial ProductsPDF (3.52mb)

CUTSHEET

-  Spec Grade GFCIs, SF1101R4PDF (394.6kb)

INSTALLATION INSTRUCTIONS

-  GFCI ReceptaclePDF (109.09kb)
-  Instalación y prueba de un tomacorriente GFCIPDF (639.9kb)
-  Installation et test d'une prise DDFTPDF (208.23kb)