



designed to be better.

# Combination Tamper-Resistant Single Pole Switch/GFCI, Ivory

1595SWTTRICC4

Deco Combo Tamper-Resistant Switch/GFCI Receptacle, 10kA SCCR, 15A/125V, Ivory

Where to buy

Like





•



•



•



## product gallery

Representative images shown.

### AVAILABLE OPTIONS



Decorator Combination Tamper-Resistant Switch/GFCI



Combination Tamper-Resistant Single Pole Switch/GFCI, Black



Combination Tamper-Resistant Single Pole Switch/GFCI, Light Almond






- SPECIFICATIONS
- RESOURCES

## features & benefits

- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- Meets 2008 National Electrical Code® Tamper-Resistant requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Up-down switching.
- 15 Amp single pole switch rated for 1/2 HP motor loads – perfect for bath or kitchen vents and garbage disposals.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.

- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

## Top 5 Resources

-  Decorator Combination Devices (Brochure)
-  Better Living Upgrades (Brochure)
-  GFCI Test & Protect (Brochure)
-  Tamper-Resistant Receptacles (Brochure)
-  Commercial & Industrial Products (Brochure)

## specifications

### General Info

- Color: Ivory
- Type: Combo Single Pole Switch/GFCI
- Special Features: Tamper-Resistant
- Style: Decorator

### Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No. 42, 111, 144
- CSA Standard: Yes
- CUL Listing No: UL943, UL498, UL20
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: UL943, UL498, UL20
- UL Standard: Yes
- U N SPS C: 39121704
- U R: No

### Dimensions

- Depth (U S): 1.13"
- Height U S: 4.2"
- Width U S: 1.72"






### Technical Information

- Amps: 15 Amp
- Volts: 120/125
- Volts A C: 125





## Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No
- 

## resources BROCHURE

-  Decorator Combination DevicesPDF (526.77kb)
-  Better Living UpgradesPDF (1.2mb)
-  GFCI Test & ProtectPDF (494.1kb)
-  Tamper-Resistant ReceptaclesPDF (791.69kb)
-  Commercial & Industrial ProductsPDF (3.52mb)

## INSTALLATION INSTRUCTIONS

-  Combination Switch/GFCI OutletPDF (267.44kb)
-  GFCI ReceptaclePDF (109.09kb)
-  Instalación y prueba de un tomacorriente GFCIPDF (639.9kb)
-  Installation et test d'une prise DDFTPDF (208.23kb)