

MjE4liBoZWlnaHQ9ljExMilgLz5kAgUPDxYCHwQFGS9hdWRpby12aWRlby9jYW1lcmFzLmFzcHhkFgICAQ8WAh8ABQdDYW1lcmFzZAIFD2QWBglBDw8WA



designed to be better.

Search

# Decorator Combination Tamper-Resistant Switch/GFCI

1595SWTTRWCC4

Deco Combo Tamper-Resistant Switch/GFCI Receptacle, 10kA SCCR, 15A/125V, White

Submit Query

Where to buy

Submit Query

Like 0 Tweet 0 0 Email Print



- 
- 
-



## product gallery

Representative images shown.

### AVAILABLE OPTIONS



Combination Tamper-Resistant Single Pole Switch/GFCI, Black



Combination Tamper-Resistant Single Pole Switch/GFCI, Ivory



Combination Tamper-Resistant Single Pole Switch/GFCI, Light Almond

- SPECIFICATIONS
- RESOURCES

### features & benefits

- Stylish rounded corners match Signature wall plates and devices.
- Sealed nightlight with high impact-resistant Lexan® lens prevents tampering.
- Nightlight uses cooler LED illumination.
- Energy-efficient LED has average 20-year life expectancy, eliminating bulb replacement.
- Photozell turns nightlight ON in dark, OFF in daylight.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Zinc-plated steel mounting strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Tri-drive screws.

### Top 5 Resources

- Decorator Combination Devices (Brochure)
- Better Living Upgrades (Brochure)
- GFCI Test & Protect (Brochure)
- Tamper-Resistant Receptacles (Brochure)
- Commercial & Industrial Products (Brochure)

### specifications

#### General Info

- Color: White
- Type: Combo Single Pole Switch/GFCI
- Special Features: Tamper-Resistant
- Style: Decorator

#### Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No. 42, 111, 144
- CSA Standard: Yes
- CUL Listing No: UL943, UL498, UL20
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: UL943, UL498, UL20
- UL Standard: Yes
- U N SPS C: 39121704
- U R: No

**Dimensions**

- Depth (U S): 1.13"
- Height U S: 4.2"
- Width U S: 1.72"






**Technical Information**

- Amps: 15 Amp
- Volts: 120/125
- Volts A C: 125





**Buy American Act Compliance**

- Country of Origin: CHINA
- Buy American Act Status: No
- 

**resources  
BROCHURE**

-  Decorator Combination DevicesPDF (526.77kb)
-  Better Living UpgradesPDF (1.2mb)
-  GFCI Test & ProtectPDF (494.1kb)
-  Tamper-Resistant ReceptaclesPDF (791.69kb)
-  Commercial & Industrial ProductsPDF (3.52mb)

**INSTALLATION INSTRUCTIONS**

-  Combination Switch/GFCI OutletPDF (267.44kb)
-  GFCI ReceptaclePDF (109.09kb)
-  Instalación y prueba de un tomacorriente GFCIPDF (639.9kb)
-  Installation et test d'une prise DDFTPDF (208.23kb)