

y5hc3B4ZBYCAgEPFgIfAAUMUG93ZXIglU3RyaXBzZAICD2QWBAIBDw8WAh8EBRQvb3JnYW5pemUtY29yZHMuYXNweGQWAmYPFgIfAAUPQ29yZCBNY



designed to be better.

Search

# Audible Alarm Tamper-Resistant GFCI Receptacle, Brown

1595TRA

Audible Alarm Tamper-Resistant GFCI Receptacle notifies end user of tripped GFCI. Provides supplemental notification (along w/Trip Indicator Light). Listed 10kA SCCR, 15A 125VAC, Brown

Submit Query

Where to buy

Submit Query

Like 0

Tweet 0

0

Email Print





## product gallery

Representative images shown.

### AVAILABLE OPTIONS



Audible Alarm Tamper-Resistant GFCI Receptacle, White



Audible Alarm Tamper-Resistant GFCI Receptacle, Black



Audible Alarm Tamper-Resistant GFCI Receptacle, Ivory



Audible Alarm Tamper-Resistant GFCI Receptacle, Light Almond

- SPECIFICATIONS
- RESOURCES

### features & benefits

- **Patented SafeLock™ Protection for More Safety** - shuts off power to the receptacle if there's a ground fault, if the GFCI is miswired, and even if the GFCI fails. This prevents the unsafe condition of power without protection.
- **Tamper-Resistant: Automatic shutter system** prevents young children from inserting common objects such as hairpins or keys.
- **The most durable GFCI available** - exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- **Audible Alarm notifies end user of tripped GFCI.** Provides Supplemental notification (along w/Trip Indicator Light - red LED). Alarm can be turned on/off.
- **Side or internal screw-pressure-plate back wire termination** speeds installation; takes #14 – #10 AWG stranded or solid, copper or copperclad conductors.
- **Two back-wire holes per termination** add wiring flexibility, eliminate pigtailing, and save box space.
- **Ground terminal back-wire clamp** for fast installation.
- **High-impact-resistant thermoplastic construction** for superior strength and durability.

### Top 5 Resources

- [Audible Alarm GFCI \(Sell Sheet\)](#)
- [Better Living Upgrades \(Brochure\)](#)
- [GFCI Test & Protect \(Brochure\)](#)
- [Tamper-Resistant Receptacles \(Brochure\)](#)
- [Commercial & Industrial Products \(Brochure\)](#)

## specifications

### General Info

- Color: Brown
- Type: Audible Alarm GFCI Receptacle
- Special Features: Tamper Resistant
- Style: Decorator

### Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- Federal Spec: No
- UL Listing No: No
- U N SPS C: 39121614
- U R: No

### Dimensions

- Depth (U S): 1.13"
- Height U S: 4.2"
- Width U S: 1.72"

### Technical Information

- Amps: 15 Amp
- Volts: 125
- Volts A C: 125

### Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
- 



### resources BROCHURE

- Better Living UpgradesPDF (1.2mb)
- GFCI Test & ProtectPDF (494.1kb)
- Tamper-Resistant ReceptaclesPDF (791.69kb)
- Commercial & Industrial ProductsPDF (3.52mb)
- GFCI ReceptaclesPDF (1.19mb)

### CUTSHEET

- Spec Grade GFCIs, SF1101R4PDF (394.6kb)

### SELL SHEET

- Audible Alarm GFCIPDF (763.88kb)

### INSTALLATION INSTRUCTIONS

- GFCI ReceptaclePDF (109.09kb)
- Instalación y prueba de un tomacorriente GFCIPDF (639.9kb)
- Installation et test d'une prise DDFTPDF (208.23kb)