



designed to be better.

# Tamper-Resistant 15 Amp GFCI, Ivory

1595TRI

GFCI Tamper-Resistant Receptacle, 10kA SCCR, 15A 125VAC, Ivory

Where to buy

Like





## product gallery

Representative images shown.

### AVAILABLE OPTIONS



Tamper-Resistant GFCI Receptacle, White



Tamper-Resistant 15 Amp GFCI, Brown



Tamper-Resistant 15 Amp GFCI, Black



Tamper-Resistant 15 Amp GFCI, Gray



Tamper-Resistant 15 Amp GFCI, Light Almond



Tamper-Resistant 15 Amp GFCI, Nickel



Tamper-Resistant 15 Amp GFCI, Titanium






- SPECIFICATIONS
- RESOURCES

## features & benefits

- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- Meets 2008 National Electrical Code® Tamper-Resistant requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.

- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

## Top 5 Resources

-  Better Living Upgrades (Brochure)
-  GFCI Test & Protect (Brochure)
-  Tamper-Resistant Receptacles (Brochure)
-  Commercial & Industrial Products (Brochure)
-  GFCI Receptacle (Installation Instructions)

## specifications

### General Info

- Color: Ivory
- Product Series: TradeMaster
- Type: GFCI Receptacle
- Special Features: Tamper-Resistant
- Style: Decorator

### Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No.42 & 144
- CSA Standard: Yes
- cU Lus: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121614

### Dimensions

- Depth (U S): 1.13"
- Height U S: 4.2"
- Width U S: 1.72"

### Technical Information





- Amps: 15 Amp
- Volts: 125
- Volts A C: 125
- Grade Type: Specification

### Buy American Act Compliance


- Country of Origin: CHINA
- Buy American Act Status: No
-

## **resources**




### **BROCHURE**

-  Better Living UpgradesPDF (1.2mb)
-  GFCI Test & ProtectPDF (494.1kb)
-  Tamper-Resistant ReceptaclesPDF (791.69kb)
-  Commercial & Industrial ProductsPDF (3.52mb)

### **CUTSHEET**

-  Spec Grade GFCIs, SF1101R4PDF (394.6kb)

### **INSTALLATION INSTRUCTIONS**

-  GFCI ReceptaclePDF (109.09kb)
-  Instalación y prueba de un tomacorriente GFCIPDF (639.9kb)
-  Installation et test d'une prise DDFTPDF (208.23kb)