

E+IDwvZGI2PiA8L2xpPiA8bGkgY2xhc3M9ImNvbDliPiA8YSBpZD0iY3RsMDVFTWFpbk5hdjFfY3RsMDJfcnB0Q29tbWVvY2lhbF9jdGwwMI9ycHRDb21tZXJjaV



designed to be better.

Search

Tamper-Resistant 15 Amp GFCI, Light Almond

1595TRLA

GFCI Tamper-Resistant Receptacle in light almond, meets 2008 National Electrical Code® Tamper-Resistant requirements. It protects children with a patented shutter system that helps prevent improper insertion of foreign objects. It has a SafeLock™ Protection that if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected. This prevents line-load reversal miswire with no power to the face or downstream receptacles if wired incorrectly. It is made with high-impact-resistant thermoplastic construction. 10kA SCCR, 15A 125VAC.

Submit Query

Where to buy

Submit Query

Like 0 Tweet 0

0 Email Print



-
-
-



product gallery
Representative images shown.
AVAILABLE OPTIONS



Tamper-Resistant GFCI Receptacle, White



Tamper-Resistant 15 Amp GFCI, Brown



Tamper-Resistant 15 Amp GFCI, Black



Tamper-Resistant 15 Amp GFCI, Gray



Tamper-Resistant 15 Amp GFCI, Ivory



Tamper-Resistant 15 Amp GFCI, Nickel



Tamper-Resistant 15 Amp GFCI, Titanium



- SPECIFICATIONS
- RESOURCES

features & benefits

- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- Meets 2008 National Electrical Code® Tamper-Resistant requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

Top 5 Resources

-  [Better Living Upgrades \(Brochure\)](#)
-  [GFCI Test & Protect \(Brochure\)](#)
-  [Tamper-Resistant Receptacles \(Brochure\)](#)
-  [Commercial & Industrial Products \(Brochure\)](#)
-  [GFCI Receptacle \(Installation Instructions\)](#)

specifications

General Info

- Color: Light Almond
- Product Series: TradeMaster
- Type: GFCI Receptacle
- Special Features: Tamper-Resistant
- Style: Decorator

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No.42 & 144
- CSA Standard: Yes
- cULus: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121614

Dimensions

- Depth (U S): 1.13"
- Height U S: 4.2"
- Width U S: 1.72"

Technical Information





- Amps: 15 Amp
- Volts: 125
- Volts A C: 125
- Grade Type: Specification

Buy American Act Compliance


- Country of Origin: CHINA
- Buy American Act Status: No
-

resources




BROCHURE

-  [Better Living UpgradesPDF \(1.2mb\)](#)
-  [GFCI Test & ProtectPDF \(494.1kb\)](#)
-  [Tamper-Resistant ReceptaclesPDF \(791.69kb\)](#)
-  [Commercial & Industrial ProductsPDF \(3.52mb\)](#)

CUTSHEET

-  [Spec Grade GFCIs, SF1101R4PDF \(394.6kb\)](#)

INSTALLATION INSTRUCTIONS

-  [GFCI ReceptaclePDF \(109.09kb\)](#)
-  [Instalación y prueba de un tomacorriente GFCIPDF \(639.9kb\)](#)
-  [Installation et test d'une prise DDFTPDF \(208.23kb\)](#)