

FVJhbmDIICyGRHJ5ZXIgt3V0bGV0c2QCaw8PFglfBAUkL2VsZWN0cmJjYWwtb3V0bGV0cy9yYW5nZS1kcmlldi5hc3B4ZBYCZg8WAh8ABX08aW1nIHJlcGxh



designed to be better.

Search

# TradeMaster® Spec Grade 15 Amp Duplex GFCI, White

1595W

TradeMaster/Spec Grade GFCI Receptacle with high-impact-resistant thermoplastic construction. It has SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected. It prevents the line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly. Its mounting screws are shipped captive in the device and wall plate for easier installation. 10kA SCCR, 15A 125VAC, White

Submit Query

Where to buy

Submit Query

Like 0 Tweet 0

0 Email Print





## product gallery

Representative images shown.

### AVAILABLE OPTIONS



TradeMaster® & Specification Grade GFCI Receptacle, Brown



TradeMaster® & Specification Grade GFCI Receptacle, Black



TradeMaster® & Specification Grade GFCI Receptacle, Gray



TradeMaster® & Specification Grade GFCI Receptacle, Ivory



TradeMaster® & Specification Grade GFCI Receptacle, Light Almond



TradeMaster® & Specification Grade GFCI Receptacle, Red

- RELATED PRODUCTS
- SPECIFICATIONS
- RESOURCES

### features & benefits

- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles. FSUL Listed (Federal Specification WC596). Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal. Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box. Extra-long strap.

- Button colors match the device face. Dual-direction test and reset buttons. Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate. Tri-drive screws.
- GFCIs with Auto-Ground assure a positive ground to metal box.

#### Top 5 Resources

- [GFCI Receptacles \(Brochure\)](#)
- [GFCI Test & Protect \(Brochure\)](#)
- [GFCI Receptacle \(Installation Instructions\)](#)
- [Instalación y prueba de un tomacorriente GFCI \(Installation Instructions\)](#)
- [Installation et test d'une prise DDFT \(Installation Instructions\)](#)

#### related products



#### NAFTA-Compliant GFCI Receptacle, White

1595NAW

[View Details](#)

#### specifications

##### General Info

- Color: White

#### Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No.42 & 144
- CSA Standard: Yes
- cU Lus: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121614

#### Dimensions

- Depth (U S): 0.98"
- Height U S: 4.2"
- Width U S: 1.72"

#### Technical Information

- Amps: 15 Amp
- Volts: 125
- Volts A C: 125

#### Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No

#### resources

##### BROCHURE

- [GFCI ReceptaclesPDF \(1.19mb\)](#)
- [GFCI Test & ProtectPDF \(494.1kb\)](#)

##### CUTSHEET

- [Spec Grade GFCIs, SF1101R4PDF \(394.6kb\)](#)

#### INSTALLATION INSTRUCTIONS

- [GFCI ReceptaclePDF \(109.09kb\)](#)
- [Instalación y prueba de un tomacorriente GFCIPDF \(639.9kb\)](#)
- [Installation et test d'une prise DDFTPDF \(208.23kb\)](#)