

pYWxfY3RsMDFfaGxTb2x1dGlvbilgaHJlZj0iL3Jlc2lkZW50aWFsL2RyZWFlLWJhdGhyb29tLmFzchGjPKRyZWFltEJhdGhyb29tczwwYT4gPC9saT4gPGxpIGNs



designed to be better.

Search

TradeMaster® & Specification Grade GFCI Receptacle, Brown

1595

TradeMaster/Spec Grade GFCI Receptacle 10KA SCCR, 15A/125V, Brown

Submit Query

Where to buy

Submit Query

Like 0

Tweet 0

0

Email Print





product gallery

Representative images shown.

AVAILABLE OPTIONS



TradeMaster® Spec Grade 15 Amp Duplex GFCI, White



TradeMaster® & Specification Grade GFCI Receptacle, Black



TradeMaster® & Specification Grade GFCI Receptacle, Gray



TradeMaster® & Specification Grade GFCI Receptacle, Ivory



TradeMaster® & Specification Grade GFCI Receptacle, Light Almond



TradeMaster® & Specification Grade GFCI Receptacle, Red








- SPECIFICATIONS
- RESOURCES

features & benefits

- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

- GFCIs with Auto-Ground assure a positive ground to metal box.

Top 5 Resources

-  [GFCI Test & Protect \(Brochure\)](#)
-  [GFCI Receptacles \(Brochure\)](#)
-  [GFCI Receptacle \(Installation Instructions\)](#)
-  [Instalación y prueba de un tomacorriente GFCI \(Installation Instructions\)](#)
-  [Installation et test d'une prise DDFT \(Installation Instructions\)](#)

specifications

General Info

- Color: Brown
- Product Series: TradeMaster
- Type: GFCI Receptacle
- Style: Decorator

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No.42 & 144
- CSA Standard: Yes
- cULus: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121614

Dimensions

- Depth (U S): 0.98"
- Height U S: 4.2"
- Width U S: 1.72"

Technical Information



- Amps: 15 Amp
- Volts: 125
- Volts A C: 120
- Grade Type: Specification

Buy American Act Compliance


- Country of Origin: CHINA
- Buy American Act Status: No
-

resources




BROCHURE

-  [GFCI Test & ProtectPDF \(494.1kb\)](#)
-  [GFCI ReceptaclesPDF \(1.19mb\)](#)

CUTSHEET

-  [Spec Grade GFCIs, SF1101R4PDF \(394.6kb\)](#)

INSTALLATION INSTRUCTIONS

-  [GFCI ReceptaclePDF \(109.09kb\)](#)
-  [Instalación y prueba de un tomacorriente GFCIPDF \(639.9kb\)](#)
-  [Installation et test d'une prise DDFTPDF \(208.23kb\)](#)