

IDxhIGlkPSJjdGwwNV9NYWluTmF2MV9jdGwwM19ycHRDb21tZXJjaWFsX2N0bDAX2hsU29sdXRpb24iIGhyZWY9li9jb21tZXJjaWFsL3Byb2R1Y3Rpdml0eS



designed to be better.

Search

Specification Grade Dead Front GFCI, Black

2085BK
GFCI DEAD FRONT, 10kA SCCR, 20A 125VAC, Black

Submit Query

Where to buy

Submit Query

Like 0

Tweet 0

0

Email Print





product gallery

Representative images shown.

AVAILABLE OPTIONS



Specification Grade Dead Front GFCI, White



Specification Grade Dead Front GFCI, Ivory



Specification Grade Dead Front GFCI, Light Almond

- SPECIFICATIONS
- RESOURCES

features & benefits

- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles. FSUL Listed (Federal Specification WC596). Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire. Two back wire holes per terminal. GFCIs with Auto-Ground assure a positive ground to metal box.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- Extra-long strap. Button colors match the device face. Dual-direction test and reset buttons. Class A rated GFCI. Supplied with matching TP26 nylon wall plate. Tri-drive screws.

Top 5 Resources

- [GFCI Test & Protect \(Brochure\)](#)
- [GFCI Receptacles \(Brochure\)](#)
- [GFCI Receptacle \(Installation Instructions\)](#)
- [Instalación y prueba de un tomacorriente GFCI \(Installation Instructions\)](#)
- [Installation et test d'une prise DDFT \(Installation Instructions\)](#)

specifications

General Info

- Color: Black
- Type: Dead Front GFCI
- Style: Decorator

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: Yes
- U N SPS C: 39121614
- U R: No

Dimensions

- Depth (U S): 0.98"
- Height U S: 4.2"
- Width U S: 1.72"

Technical Information

- Amps: 20 Amp
- Volts: 125



- Volts A C: 125
- Grade Type: Specification

Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No
-

resources




BROCHURE

-  [GFCI Test & ProtectPDF \(494.1kb\)](#)
-  [GFCI ReceptaclesPDF \(1.19mb\)](#)

CUTSHEET

-  [Spec Grade Dead Front GFCIs, SF1103R3PDF \(321.92kb\)](#)

INSTALLATION INSTRUCTIONS

-  [GFCI ReceptaclePDF \(109.09kb\)](#)
-  [Instalación y prueba de un tomacorriente GFCIPDF \(639.9kb\)](#)
-  [Installation et test d'une prise DDFTPDF \(208.23kb\)](#)