



designed to be better.

# Specification Grade Dead Front GFCI, Light Almond

2085LA

GFCI DEAD FRONT, 10kA SCCR, 20A 125VAC, Light Almond

Where to buy

Like





## product gallery

Representative images shown.

## AVAILABLE OPTIONS



Specification Grade Dead Front GFCI, White



Specification Grade Dead Front GFCI, Black



Specification Grade Dead Front GFCI, Ivory






- SPECIFICATIONS
- RESOURCES

## features & benefits

- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles. FSUL Listed (Federal Specification WC596). Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire. Two back wire holes per terminal. GFCIs with Auto-Ground assure a positive ground to metal box.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.

- Extra-long strap. Button colors match the device face. Dual-direction test and reset buttons. Class A rated GFCI. Supplied with matching TP26 nylon wall plate. Tri-drive screws.

## Top 5 Resources

-  GFCI Test & Protect (Brochure)
-  GFCI Receptacles (Brochure)
-  GFCI Receptacle (Installation Instructions)
-  Instalación y prueba de un tomacorriente GFCI (Installation Instructions)
-  Installation et test d'une prise DDFT (Installation Instructions)

## specifications

### General Info

- Color: Light Almond
- Type: Dead Front GFCI
- Style: Decorator

### Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: Yes
- U N SPS C: 39121614
- U R: No

### Dimensions

- Depth (U S): 0.98"
- Height U S: 4.2"
- Width U S: 1.72"

### Technical Information



- Amps: 20 Amp
- Volts: 125
- Volts A C: 125
- Grade Type: Specification

### Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No
- 

## resources




### BROCHURE

-  GFCI Test & ProtectPDF (494.1kb)
-  GFCI ReceptaclesPDF (1.19mb)

## CUTSHEET

 Spec Grade Dead Front GFCIs, SF1103R3PDF (321.92kb)

## INSTALLATION INSTRUCTIONS

-  GFCI ReceptaclePDF (109.09kb)
-  Instalación y prueba de un tomacorriente GFCIPDF (639.9kb)
-  Installation et test d'une prise DDFTPDF (208.23kb)