



designed to be better.

Specification Grade Dead Front GFCI, White

2085W

Decorator devices combine today's design aesthetics - with ease of installation, reliability, and performance that never goes out of style. Rated as a 1-1/2 HP motor control switch. SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to the load is disconnected. Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.

Where to buy

Like







product gallery

Representative images shown.

AVAILABLE OPTIONS



Specification Grade Dead Front GFCI, Black



Specification Grade Dead Front GFCI, Ivory



Specification Grade Dead Front GFCI, Light Almond






- SPECIFICATIONS
- RESOURCES

features & benefits

- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles. FSUL Listed (Federal Specification WC596). Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire. Two back wire holes per terminal. GFCIs with Auto-Ground assure a positive ground to metal box.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.

- Extra-long strap. Button colors match the device face. Dual-direction test and reset buttons. Class A rated GFCI. Supplied with matching TP26 nylon wall plate. Tri-drive screws.

Top 5 Resources

-  GFCI Test & Protect (Brochure)
-  GFCI Receptacles (Brochure)
-  GFCI Receptacle (Installation Instructions)
-  Instalación y prueba de un tomacorriente GFCI (Installation Instructions)
-  Installation et test d'une prise DDFT (Installation Instructions)

specifications

General Info

- Color: White
- Type: Dead Front GFCI
- Style: Decorator

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: Yes
- U N SPS C: 39121614
- U R: No

Dimensions

- Depth (U S): 0.98"
- Height U S: 4.2"
- Width U S: 1.72"

Technical Information



- Amps: 20 Amp
- Volts: 125
- Volts A C: 125
- Grade Type: Specification

Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No
-

resources




BROCHURE

-  GFCI Test & ProtectPDF (494.1kb)
-  GFCI ReceptaclesPDF (1.19mb)

CUTSHEET

 [Spec Grade Dead Front GFCIs, SF1103R3PDF \(321.92kb\)](#)

INSTALLATION INSTRUCTIONS

-  [GFCI ReceptaclePDF \(109.09kb\)](#)
-  [Instalación y prueba de un tomacorriente GFCIPDF \(639.9kb\)](#)
-  [Installation et test d'une prise DDFTPDF \(208.23kb\)](#)