



designed to be better.

Specification Grade GFCI Receptacle, Gray

2095GRY
GFCI Receptacle, 10kA SCCR, 20A/125VAC, Gray

Where to buy

Like





product gallery

Representative images shown.

AVAILABLE OPTIONS



Specification Grade 20 Amp Duplex GFCI, White



Specification Grade GFCI Receptacle, Brown



Specification Grade GFCI Receptacle, Black



Specification Grade GFCI Receptacle, Ivory



Specification Grade GFCI Receptacle, Light Almond








Specification Grade GFCI Receptacle, Red

- SPECIFICATIONS
- RESOURCES

features & benefits

- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal.
- Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.
- GFCIs with Auto-Ground assure a positive ground to metal box.

Top 5 Resources

-  [GFCI Test & Protect \(Brochure\)](#)
-  [GFCI Receptacles \(Brochure\)](#)
-  [GFCI Receptacle \(Installation Instructions\)](#)
-  [Instalación y prueba de un tomacorriente GFCI \(Installation Instructions\)](#)
-  [Installation et test d'une prise DDFT \(Installation Instructions\)](#)

specifications

General Info

- Color: Gray
- Type: GFCI Receptacle
- Style: Decorator

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No. 42 & 144
- CSA Standard: Yes
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL943 & UL498
- UL Standard: Yes
- U N SPS C: 39121614
- U R: No

Dimensions

- Depth (U S): 0.98"
- Height U S: 4.2"
- Width U S: 1.72"



Technical Information

- Amps: 20 Amp
- Volts: 125
- Volts A C: 125
- Grade Type: Specification


Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No
-




resources BROCHURE

-  GFCI Test & ProtectPDF (494.1kb)
-  GFCI ReceptaclesPDF (1.19mb)

CUTSHEET

-  Spec Grade GFCIs, SF1101R4PDF (394.6kb)

INSTALLATION INSTRUCTIONS

-  GFCI ReceptaclePDF (109.09kb)
-  Instalación y prueba de un tomacorriente GFCIPDF (639.9kb)
-  Installation et test d'une prise DDFTPDF (208.23kb)