



designed to be better.

# Hospital Grade 20 Amp Duplex GFCI, White

2095HGW

Our complete line of Decorator devices combine today's design aesthetics - with ease of installation, reliability, and performance that never goes out of style. SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected. Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.

Where to buy

Like

Tweet





## product gallery

Representative images shown.

## AVAILABLE OPTIONS

Hospital Grade GFCI Receptacle, Brown

Hospital Grade GFCI Receptacle, Black

Hospital Grade GFCI Receptacle, Gray

Hospital Grade GFCI Receptacle, Ivory

Hospital Grade GFCI Receptacle, Light Almond






Hospital Grade GFCI Receptacle, Red

- SPECIFICATIONS
- RESOURCES

## features & benefits

- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles. FSUL Listed (Federal Specification WC596). Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire. Two back wire holes per terminal.
- 10kA SCCR, 20A/125VAC
- Ground screw has a back wire clamp for easy installation. 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box.
- Mounting screws are shipped captive in the device and wall plate for easier installation. High-impact-resistant thermoplastic construction.
- Extra-long strap. Button colors match the device face. Dual-direction test and reset buttons. Class A rated GFCI. Supplied with matching TP26 nylon wall plate. Tri-drive screws.

## Top 5 Resources

-  [GFCI Receptacles \(Brochure\)](#)
-  [GFCI Test & Protect \(Brochure\)](#)
-  [GFCI Receptacle \(Installation Instructions\)](#)
-  [Instalación y prueba de un tomacorriente GFCI \(Installation Instructions\)](#)
-  [Installation et test d'une prise DDFT \(Installation Instructions\)](#)

## specifications

### General Info

- Color: White
- Type: GFCI Receptacle
- Style: Decorator

### Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No.42 & 144
- CSA Standard: Yes
- CUL Listing No: UL943, UL498
- cU Lus: Yes
- cUL Standard: Yes
- cU Rus: No
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL943, UL498
- UL Standard: Yes
- U N SPS C: 39121614
- U R: No

### Dimensions

- Depth (U S): 0.98"
- Height U S: 4.2"
- Width U S: 1.72"

### Technical Information



- Amps: 20 Amp
- Volts: 125
- Volts A C: 125
- Grade Type: Hospital

### Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No
- 

## resources

### BROCHURE



-  [GFCI ReceptaclesPDF \(1.19mb\)](#)
-  [GFCI Test & ProtectPDF \(494.1kb\)](#)

### CUTSHEET

-  [Hospital Grade GFCIs Spec Sheet, SF708R3PDF \(375.45kb\)](#)

### INSTALLATION INSTRUCTIONS

-  [GFCI ReceptaclePDF \(109.09kb\)](#)

-  Instalación y prueba de un tomacorriente GFCIPDF (639.9kb)
-  Installation et test d'une prise DDFTPDF (208.23kb)