

3JwdENvbW1lcmNpYWxfY3RzMDFfaGxTb2x1dGlvbilgaHJlZj0iL2NvbW1lcmNpYWwvcHJvZHVjdGl2aXR5LWNvcn5lci5hc3B4Ij5Db250cmFjdG9yIFByb2R1Y:



designed to be better.

Search

# Hospital Grade GFCI Receptacle, Brown

2095HG

GFCI Hospital Grade Receptacle, 10kA SCCR, 20A 125VAC, Brown

Submit Query

Where to buy

Submit Query

Like 0

Tweet 0

0

Email Print





## product gallery

Representative images shown.

### AVAILABLE OPTIONS

Hospital Grade 20 Amp Duplex GFCI, White

Hospital Grade GFCI Receptacle, Black

Hospital Grade GFCI Receptacle, Gray

Hospital Grade GFCI Receptacle, Ivory

Hospital Grade GFCI Receptacle, Light Almond

Hospital Grade GFCI Receptacle, Red






- SPECIFICATIONS
- RESOURCES

### features & benefits

- **Patented SafeLock™ Protection for More Safety** - shuts off power to the receptacle if there's a ground fault, if the GFCI is miswired, and even if the GFCI fails. This prevents the unsafe condition of power without protection.
- **Tamper-Resistant: Automatic shutter system** prevents young children from inserting common objects such as hairpins or keys.
- **The most durable GFCI available** - exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- **Audible Alarm notifies end user of tripped GFCI.** Provides Supplemental notification (along w/Trip Indicator Light - red LED). Alarm can be turned on/off.
- **Side or internal screw-pressure-plate back wire termination** speeds installation; takes #14 – #10 AWG stranded or solid, copper or copperclad conductors.

- **Two back-wire holes per termination** add wiring flexibility, eliminate pigtailling, and save box space.
- **Ground terminal back-wire clamp** for fast installation.
- **High-impact-resistant thermoplastic construction** for superior strength and durability.

### Top 5 Resources

-  [GFCI Test & Protect \(Brochure\)](#)
-  [GFCI Receptacles \(Brochure\)](#)
-  [GFCI Receptacle \(Installation Instructions\)](#)
-  [Instalación y prueba de un tomacorriente GFCI \(Installation Instructions\)](#)
-  [Installation et test d'une prise DDFT \(Installation Instructions\)](#)

## specifications

### General Info

- Color: Brown
- Type: GFCI Receptacle
- Style: Decorator

### Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No.42 & 144
- CSA Standard: Yes
- CUL Listing No: UL943, UL498
- cUL Lus: Yes
- cUL Standard: Yes
- cUL Rus: No
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL943, UL498
- UL Standard: Yes
- U N SPS C: 39121614
- U R: No

### Dimensions

- Depth (U S): 0.98"
- Height U S: 4.2"
- Width U S: 1.72"

### Technical Information



- Amps: 20 Amp
- Volts: 125
- Volts A C: 125
- Grade Type: Hospital

### Buy American Act Compliance


- Country of Origin: CHINA
- Buy American Act Status: No
- 

## resources




### BROCHURE

-  [GFCI Test & ProtectPDF \(494.1kb\)](#)
-  [GFCI ReceptaclesPDF \(1.19mb\)](#)

### CUTSHEET

-  [Hospital Grade GFCIs Spec Sheet, SF708R3PDF \(375.45kb\)](#)

### INSTALLATION INSTRUCTIONS

-  [GFCI ReceptaclePDF \(109.09kb\)](#)
-  [Instalación y prueba de un tomacorriente GFCIPDF \(639.9kb\)](#)
-  [Installation et test d'une prise DDFTPDF \(208.23kb\)](#)