



designed to be better.

 Search

Isolated Ground Hospital Grade Tamper-Resistant GFCI Receptacle, Orange

2095IGHGTRO

Isolated Ground Hospital Grade Tamper-Resistant GFCI Receptacle provides plastic barrier that isolates grounding terminal from mounting strap and metal boxes to minimize electrical noise. Listed 10kA SCCR, 20A 125VAC, Orange.

Submit Query

Where to buy

Submit Query

Like

Tweet

 
Email Print





product gallery

Representative images shown.

AVAILABLE OPTIONS



Isolated Ground Hospital Grade Tamper-Resistant GFCI Receptacle, White



Isolated Ground Hospital Grade Tamper-Resistant GFCI Receptacle, Brown



Isolated Ground Hospital Grade Tamper-Resistant GFCI Receptacle, Gray



Isolated Ground Hospital Grade Tamper-Resistant GFCI Receptacle, Ivory



Isolated Ground Hospital Grade Tamper-Resistant GFCI Receptacle, Light Almond



Isolated Ground Hospital Grade Tamper-Resistant GFCI Receptacle, Red

- SPECIFICATIONS
- RESOURCES

features & benefits

- **Patented SafeLock™ Protection for More Safety** - shuts off power to the receptacle if there's a ground fault, if the GFCI is miswired, and even if the GFCI fails. This prevents the unsafe condition of power without protection.
- **Automatic Shutter system** prevents young children from inserting common objects such as hairpins or keys.
- **The most durable GFCI available** - exceeds UL943 voltage surge requirements; survives 100X the required UL 3kA/6kV voltage surge test cycles.
- **Side or internal screw-pressure plate back-wire termination** speeds installation; takes #14 - #10 AWG stranded or solid, copper or copperclad conductors.
- **Two back-wire holes per termination** add wiring flexibility, eliminate pigtail, and save box space.
- **Pre-stripped stranded wire lead** for isolated ground termination.
- **Trip indicator light** makes it easy to identify a tripped condition.
- **GFCI Receptacle's grounding system is isolated** from the building's grounding system.

Top 5 Resources

-  Isolated Ground GFCI (Sell Sheet)
-  GFCI Test & Protect (Brochure)
-  Tamper-Resistant Receptacles (Brochure)
-  Commercial & Industrial Products (Brochure)
-  GFCI Receptacle (Installation Instructions)

specifications

General Info

- Color: Orange
- Type: GFCI Receptacle
- Special Features: Isolated Ground, Tamper-Resistant
- Style: Decorator

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: Yes
- U N SPS C: 39121614
- U R: No

Dimensions

- Depth (U S): 1.13"
- Height U S: 4.2"
- Width U S: 1.72"

Technical Information




- Amps: 20 Amp
- Volts: 125
- Volts A C: 125
- Grade Type: Hospital

Buy American Act Compliance


- Country of Origin: CHINA
- Buy American Act Status: No
-

resources


BROCHURE

-  GFCI Test & ProtectPDF (494.1kb)
-  Tamper-Resistant ReceptaclesPDF (791.69kb)
-  Commercial & Industrial ProductsPDF (3.52mb)




CUTSHEET

 Spec Grade GFCIs, SF1101R4PDF (394.6kb)

SELL SHEET

 Isolated Ground GFCIPDF (698.49kb)

INSTALLATION INSTRUCTIONS

-  GFCI ReceptaclePDF (109.09kb)
-  Instalación y prueba de un tomacorriente GFCIPDF (639.9kb)
-  Installation et test d'une prise DDFTPDF (208.23kb)