

ocmVmPSlvd2lyZS1jYWJsZS1tYW5hZ2VtZW50L21vZHVzYXItZD2lyaW5nLmFzCHgiPjxpbWcgcmVwbGFjZT0iZHNyYylgZHNyYz0iL34vbWVkaWEvMkE3RjI0N



designed to be better.

Search

Audible Alarm Tamper-Resistant GFCI Receptacle, White

2095TRAW

Hospital Grade Audible Alarm Tamper-Resistant GFCI Receptacle notifies end user of tripped GFCI. Provides supplemental notification (along w/Trip Indicator Light). Listed 10KA SCCR, 60 dB at 10 feet, 15A 125VAC, Brown

Submit Query

Where to buy Enter Postal Code

Submit Query

Like 0

Tweet 0

0

Email Print





product gallery

Representative images shown.

AVAILABLE OPTIONS



Audible Alarm Tamper-Resistant GFCI Receptacle, Brown



Audible Alarm Tamper-Resistant GFCI Receptacle, Black



Audible Alarm Tamper-Resistant GFCI Receptacle, Gray



Audible Alarm Tamper-Resistant GFCI Receptacle, Ivory



Audible Alarm Tamper-Resistant GFCI Receptacle, Light Almond



Audible Alarm Tamper-Resistant GFCI Receptacle, Red

- SPECIFICATIONS

- RESOURCES

features & benefits

- **Patented SafeLock™ Protection for More Safety** - shuts off power to the receptacle if there's a ground fault, if the GFCI is miswired, and even if the GFCI fails. This prevents the unsafe condition of power without protection.
- **Tamper-Resistant: Automatic shutter system** prevents young children from inserting common objects such as hairpins or keys.
- **The most durable GFCI available** - exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- **Audible Alarm notifies end user of tripped GFCI.** Provides Supplemental notification (along w/Trip Indicator Light - red LED). Alarm can be turned on/off.
- **Side or internal screw-pressure-plate back wire termination** speeds installation; takes #14 – #10 AWG stranded or solid, copper or copperplated conductors.
- **Two back-wire holes per termination** add wiring flexibility, eliminate pigtailing, and save box space.
- **Ground terminal back-wire clamp** for fast installation.
- **High-impact-resistant thermoplastic construction** for superior strength and durability.

Top 5 Resources

-  Audible Alarm GFCI (Sell Sheet)
-  GFCI Test & Protect (Brochure)
-  Tamper-Resistant Receptacles (Brochure)
-  Commercial & Industrial Products (Brochure)
-  GFCI Receptacle (Installation Instructions)

specifications

General Info

- Color: White
- Type: GFCI Receptacle w/Audible Alarm
- Special Features: Tamper-Resistant
- Style: Decorator

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No.42 & 144
- CSA Standard: Yes
- cULus: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL943, UL498
- UL Standard: Yes
- U N SPS C: 39121614

Dimensions

- Depth (U S): 1.13"
- Height U S: 4.2"
- Width U S: 1.72"

Technical Information

- Amps: 20 Amp
- Volts: 125
- Volts A C: 125




Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-




resources

BROCHURE

-  GFCI Test & ProtectPDF (494.1kb)
-  Tamper-Resistant ReceptaclesPDF (791.69kb)
-  Commercial & Industrial ProductsPDF (3.52mb)




CUTSHEET

-  Spec Grade GFCIs, SF1101R4PDF (394.6kb)

SELL SHEET

-  Audible Alarm GFCIPDF (763.88kb)

INSTALLATION INSTRUCTIONS

-  GFCI ReceptaclePDF (109.09kb)
-  Instalación y prueba de un tomacorriente GFCIPDF (639.9kb)
-  Installation et test d'une prise DDFTPDF (208.23kb)