

YXJtb255L2RjbDQ1M3B0Yy5hc3B4ZBYCZg8PZBYEHwUFBGRzcmMfBgVDL34vbWVkaWEvMDNGODI1QkJBjRjJBNDJCMUJENUJzNkUwNDkwQkM4NTMu



designed to be better.

[Search](#)

# Tamper-Resistant GFCI Receptacle, Light Almond

2095TRLA

GFCI Tamper-Resistant Receptacle, 10kA SCCR, 20A 125VAC, Light Almond

[Submit Query](#)

Where to buy

[Submit Query](#)

Like  Tweet

[Email](#) [Print](#)





•



•



•

### product gallery

Representative images shown.

### AVAILABLE OPTIONS



Tamper-Resistant GFCI Receptacle, Brown



Tamper-Resistant GFCI Receptacle, Black



Tamper-Resistant GFCI Receptacle, Gray



Tamper-Resistant GFCI Receptacle, Ivory








Tamper-Resistant GFCI Receptacle, Red

- SPECIFICATIONS
- RESOURCES

## features & benefits

- Stylish rounded corners match Signature wall plates and devices.
- Tamper-resistant models have dual mechanical shutter system to help prevent insertion of foreign objects.
- Sealed nightlight with high impact-resistant Lexan® lens prevents tampering.
- Nightlight uses cooler LED illumination.
- Energy-efficient LED has average 20-year life expectancy, eliminating bulb replacement.
- Photozell turns nightlight ON in dark, OFF in daylight. SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- FSUL Listed (Federal Specification WC596).
- Trip indicator light (red LED).
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Zinc-plated steel mounting strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Tri-drive screws.

## Top 5 Resources

-  [GFCI Test & Protect \(Brochure\)](#)
-  [Tamper-Resistant Receptacles \(Brochure\)](#)
-  [Commercial & Industrial Products \(Brochure\)](#)
-  [GFCI Receptacle \(Installation Instructions\)](#)
-  [Instalación y prueba de un tomacorriente GFCI \(Installation Instructions\)](#)

## specifications

### General Info

- Color: Light Almond
- Type: GFCI Receptacle
- Special Features: Tamper-Resistant
- Style: Decorator

### Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No.42 & 144
- CSA Standard: Yes
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498 & UL943
- UL Standard: Yes
- U N SPS C: 39121614
- U R: No

### Dimensions

- Depth (U S): 1.13"
- Height U S: 4.2"
- Width U S: 1.72"

### Technical Information




- Amps: 20 Amp
- Volts: 125
- Volts A C: 125
- Grade Type: Specification

### Buy American Act Compliance


- Country of Origin: CHINA
- Buy American Act Status: No

## resources




### BROCHURE

-  [GFCI Test & ProtectPDF \(494.1kb\)](#)
-  [Tamper-Resistant ReceptaclesPDF \(791.69kb\)](#)
-  [Commercial & Industrial ProductsPDF \(3.52mb\)](#)

### CUTSHEET

-  [Spec Grade GFCIs, SF1101R4PDF \(394.6kb\)](#)

### INSTALLATION INSTRUCTIONS

-  [GFCI ReceptaclePDF \(109.09kb\)](#)
-  [Instalación y prueba de un tomacorriente GFCIPDF \(639.9kb\)](#)
-  [Installation et test d'une prise DDFTPDF \(208.23kb\)](#)