

YWNIPSJkc3JjliBkc3JjPSlvi9tZWRpYS9FOENDMDZDNjk1OTI0Nki2OTNDNkFCREY1MTJDRDU1MC5hc2h4liBhbHQ9IiJiY2VwdGFjbGVzliB3aWR0aD0iMjE



designed to be better.

Search

# Weather-Resistant GFCI Receptacle, White

2095TRWRW

GFCI Receptacle Tamper-Resistant/Weather-Resistant, 10kA SCCR, 20A 120V, White

Submit Query

Where to buy

Submit Query

Like 0 Tweet 0 0 Email Print



- 
- 
-



## product gallery

Representative images shown.

## AVAILABLE OPTIONS

Weather-Resistant/Tamper-Resistant GFCI Receptacle, Brown

Weather-Resistant GFCI Receptacle, Black

Weather-Resistant GFCI Receptacle, Gray

Weather-Resistant GFCI Receptacle, Ivory

Weather-Resistant GFCI Receptacle, Light Almond

- SPECIFICATIONS
- RESOURCES

## features & benefits

- **Patented SafeLock™ Protection for More Safety** - shuts off power to the receptacle if there's a ground fault, if the GFCI is miswired, and even if the GFCI fails. This prevents the unsafe condition of power without protection.
- **Tamper-Resistant: Automatic shutter system** prevents young children from inserting common objects such as hairpins or keys.
- **The most durable GFCI available** - exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- **Audible Alarm notifies end user of tripped GFCI.** Provides Supplemental notification (along w/Trip Indicator Light - red LED). Alarm can be turned on/off.
- **Side or internal screw-pressure-plate back wire termination** speeds installation; takes #14 – #10 AWG stranded or solid, copper or copperclad conductors.
- **Two back-wire holes per termination** add wiring flexibility, eliminate pigtail, and save box space.
- **Ground terminal back-wire clamp** for fast installation.
- **High-impact-resistant thermoplastic construction** for superior strength and durability.

## Top 5 Resources

- [Tamper-Resistant Receptacles \(Brochure\)](#)
- [GFCI Receptacles \(Brochure\)](#)
- [GFCI Test & Protect \(Brochure\)](#)
- [GFCI Receptacle \(Installation Instructions\)](#)
- [Instalación y prueba de un tomacorriente GFCI \(Installation Instructions\)](#)

## specifications

### General Info

- Color: White
- Type: GFCI Receptacle
- Special Features: Weather-Resistant, Tamper-Resistant
- Style: Decorator

### Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No.42 & 144
- CSA Standard: Yes
- cULus: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL943, UL498
- UL Standard: Yes
- U N SPS C: 39121614

### Dimensions

- Depth (U S): 1.13"
- Height U S: 4.2"
- Width U S: 1.72"

### Technical Information




- Amps: 20 Amp
- Volts: 125
- Volts A C: 125

### Buy American Act Compliance




- Country of Origin: CHINA
- Buy American Act Status: No
- 

## resources

### BROCHURE

-  Tamper-Resistant ReceptaclesPDF (791.69kb)
-  GFCI ReceptaclesPDF (1.19mb)
-  GFCI Test & ProtectPDF (494.1kb)

### INSTALLATION INSTRUCTIONS

-  GFCI ReceptaclePDF (109.09kb)
-  Instalación y prueba de un tomacorriente GFCIPDF (639.9kb)
-  Installation et test d'une prise DDFTPDF (208.23kb)