

VtZW50L2ZpcmVzdG9wLWZpdHRpbmdzLmFzcHgiPIZpZXcgRmlyZXN0b3AgRml0dGluZ3M8L2E+IDwvZGI2PiA8L2xpPiA8bGkgY2xhc3M9ImNvbDliPiA8YSB



designed to be better.

[Search](#)  
2095TRW

Where to buy

0  0





**product gallery**  
Representative images shown.  
**AVAILABLE OPTIONS**



Tamper-Resistant GFCI Receptacle, Brown



Tamper-Resistant GFCI Receptacle, Black



Tamper-Resistant GFCI Receptacle, Gray



Tamper-Resistant GFCI Receptacle, Ivory



Tamper-Resistant GFCI Receptacle, Light Almond



Tamper-Resistant GFCI Receptacle, Red

- SPECIFICATIONS
- RESOURCES

**specifications**  
**General Info**

- Color: White
- Type: GFCI Receptacle

**Listing Agencies/Third Party Information**

- CSA Listing Info: No
- CUL Listing No: No
- cULus: Yes
- cURus: No
- Federal Spec: No
- UL Listing No: Yes
- U N SPS C: 39121614
- U R: No

**Dimensions**

- Depth (U S): 1.13"
- Height U S: 4.2"
- Width U S: 1.72"




**Technical Information**

- Amps: 20 Amp
- Volts: 125
- Volts A C: 125


**Buy American Act Compliance**

- Country of Origin: CHINA
- Buy American Act Status: No
- 




**resources****BROCHURE**

-  [GFCI Test & ProtectPDF \(494.1kb\)](#)
-  [Tamper-Resistant ReceptaclesPDF \(791.69kb\)](#)
-  [Commercial & Industrial ProductsPDF \(3.52mb\)](#)

**CUTSHEET**

-  [Spec Grade GFCIs, SF1101R4PDF \(394.6kb\)](#)

**INSTALLATION INSTRUCTIONS**

-  [GFCI ReceptaclePDF \(109.09kb\)](#)
-  [Instalación y prueba de un tomacorriente GFCIPDF \(639.9kb\)](#)
-  [Installation et test d'une prise DDFTPDF \(208.23kb\)](#)