

pbk5hdjFfY3RsMDRfcnB0UmVzb3VyY2VzMV9jdGwwMF9obFJlc291cmNITGlualyIgaHJlZj0iL3Jlc291cmNlcy1hbmQtZG93bmxvYWZRzL2JpbS1vYmplY3RzLmF



designed to be better.

Search

Cat 5e Patch Panel, patch panel, data modules, Cat 5e 24 port Cat 5e patch panel, 24 port patch panel Cat 5e 24-Port Rack Mount Patch Panel

24845C5E

This 24 port universal 568A/B Category 5e rack mount patch panel takes up a single rack space (1U). The patch panel performance exceeds the TIA Category 5e Patch Panel Standards. It supports data rates up to 10 Gigabits. It offers many cable management features such as rear cable management bar, cable ties for strain relief, and front facing labels.

MSRP

\$176.67 USD

Submit Query

Where to buy Enter Postal Code

Submit Query

0



Representative image shown.

- RELATED PRODUCTS
- SPECIFICATIONS

features & benefits

- Supports 24 network connections up to 10 Gigabit Ethernet speeds.
- Included Cable Management bar secures rear cables and provide strain relief.
- Exceeds the TIA/EIA-568 standard for connecting hardware.

related products

7 Foot Cat 5e Patch Cable, White

AC3507-WH-V1

[View Details](#)

RJ45 Cat 5e QC Keystone Insert, White

WP3475-WH

[View Details](#)

specifications

General Info

- Cable Type: Cat 5e
- Color: Black
- Mod Jack Wiring: T568A/B Universal Wiring
- Type: Rackmount Patch Panel
- Input Plug Type: RJ45 Male

Listing Agencies/Third Party Information

- cU Lus: Yes
- FCC Standard: Yes
- Fed Spec Number: FCC Part 68
- U N SPS C: 43223309

Dimensions

- Depth (Metric): 8 cm
- Depth (U S): 3 in
- Height Metric: 4.445 cm
- Height U S: 1.75 in
- Width Metric: 48 cm
- Width U S: 19 in

Technical Information

- Material: Plastic and Steel
- Mounting: Rack
- Performance Rating: High-performance panel
- Product Fits Into: 19-inch rack
- Receptacle Type: RJ45 Female, 8P8C
- Number of Receptacles: 24