




designed to be better.

 Search

Specification Grade Decorator Switch, Light Almond

2621LA

Single Pole, Back and Side Wire, Decorator Switch, 120/277 volts, Light Almond.

Submit Query

Where to buy

Submit Query

Like

Tweet

 
Email Print



•



•



•

.

product gallery

Representative images shown.

AVAILABLE OPTIONS

Specification Grade Decorator Switch

Specification Grade Decorator Switch

Specification Grade Decorator Switch

Specification Grade Decorator Switch, Black

Specification Grade Decorator Switch, Gray

Specification Grade Decorator Switch, Ivory

Specification Grade Decorator Switch, Light Almond

Specification Grade Decorator Switch, White

Specification Grade Decorator Switch, Ivory

Specification Grade Decorator Switch, Light Almond

Specification Grade Decorator Switch, White

Specification Grade Decorator Switch, Brown

Specification Grade Decorator Switch

Specification Grade Decorator Switch

Specification Grade Decorator Switch

Specification Grade Decorator Switch

Specification Grade Decorator Switch

Specification Grade Decorator Switch

Specification Grade Decorator Switch, Black

Specification Grade Decorator Switch, Gray

Specification Grade Decorator Switch, Ivory

Specification Grade Decorator Switch, Red

Specification Grade Decorator Switch, White

Specification Grade Decorator Switch, Brown

Specification Grade Decorator Switch, Black

Specification Grade Decorator Switch, Gray

Specification Grade Decorator Switch, Ivory

Specification Grade Decorator Switch, Light Almond



Specification Grade Decorator Switch, White

- SPECIFICATIONS
- RESOURCES

features & benefits

- Impact-resistant polycarb back body and frame.
- Cushioned thermoplastic paddle assures smooth, quiet, long term operation.
- Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.
- Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.
- Terminals made of high conductivity brass and serrated for maximum wire gripping.
- Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.
- Integral auto-ground clip for positive ground to metal boxes.
- Tri-drive ground, terminal, and mounting screws.
- All terminal screws backed out, ready-to-install.

Top 5 Resources

-  [Commercial & Industrial Products \(Brochure\)](#)
-  [Decorator Switches, SF901R1 \(Cutsheet\)](#)

specifications

General Info

- Number Of Poles: 1
- Style: Decorator

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 111
- CSA Standard: Yes
- UL Listing No: 20
- UL Standard: Yes
- U N SPS C: 39121507

Dimensions

- Depth (U S): 1.06"
- Height U S: 3.531"
- Width U S: 1.3"

Technical Information

- Amps: 15 Amp
- Volts: 120/277VAC
- Volts A C: 120/277


Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-

resources BROCHURE

 Commercial & Industrial ProductsPDF (3.52mb)

CUTSHEET

 Decorator Switches, SF901R1PDF (300.66kb)