

HRDb21tZXJjaWFsX2N0bDAxX3JwdENvbW1lcmNpYWxTdWJtZW51X2N0bDA2X2hsVmld0ltYWdlTGluaylgaHJlZj0iL2RhdGFjb20vc3VyZ2UtcHJvdGVjdGI2Z



designed to be better.

Search

# Heavy-Duty Decorator Spec Grade Receptacles, Side Wire, 20A, 125V, Ivory

26342I

Heavy-Duty Decorator Spec Grade Duplex Receptacle Side Wire 20amp 125volt Ivory

Submit Query

Where to buy

Enter Postal Code

Submit Query

0



Representative image shown.

## AVAILABLE OPTIONS



Heavy-Duty Decorator Spec Grade Receptacles, Side Wire, 20A, 125V, White



Heavy-Duty Decorator Spec Grade Receptacles, Side Wire, 20A, 125V, Black



Heavy-Duty Decorator Spec Grade Receptacles, Side Wire, 20A, 125V, Gray



Heavy-Duty Decorator Spec Grade Receptacles, Side Wire, 20A, 125V, Red

- SPECIFICATIONS
- RESOURCES

## features & benefits

- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.
- One-piece, brass, triple-wipe power contacts for lasting retention.
- Heavy-duty compact design for easier installation and long lasting performance.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face.

- Terminal compartments isolated from each other for positive conductor containment.
- Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.
- All devices fit standard #26 opening wall plate.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.

### Top 5 Resources

 Commercial & Industrial Products (Brochure)

### specifications

#### General Info

- Color: Ivory
- Type: Receptacles
- Duty: Heavy Duty
- Special Features: Side Wire
- Style: Decorator

#### Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: Yes
- cU Lus: No
- cU Rus: No
- Federal Spec: Yes
- UL Listing No: No
- U N SPS C: 39121406
- U R: No

#### Dimensions

- Depth (U S): 0.833"
- Height U S: 3.281"
- Width U S: 1.322"

#### Technical Information

- Amps: 20 Amp
- Volts: 125V
- Volts A C: 125
- Capacity: Duplex
- Grade Type: Specification

#### Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
- 



### resources

#### BROCHURE

 Commercial & Industrial ProductsPDF (3.52mb)