



designed to be better.

Search

# Heavy-Duty Decorator Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Ivory

26352I

Heavy-Duty Decorator Spec Grade Duplex Receptacle Back & Side Wire 20amp 125volt Ivory

Where to buy

0



Representative image shown.

## AVAILABLE OPTIONS



Heavy-Duty Decorator Spec Grade Receptacles, Back & Side Wire, 20A, 125V, White



Heavy-Duty Decorator Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Brown



Heavy-Duty Decorator Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Black



Heavy-Duty Decorator Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Gray



Heavy-Duty Decorator Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Light Almond





Heavy-Duty Decorator Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Red

- SPECIFICATIONS
- RESOURCES

## features & benefits

- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.
- One-piece, brass, triple-wipe power contacts for lasting retention.
- Heavy-duty compact design for easier installation and long lasting performance.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face.
- Terminal compartments isolated from each other for positive conductor containment.
- Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.
- All devices fit standard #26 opening wall plate.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.

## Top 5 Resources

-  Commercial & Industrial Products (Brochure)
-  Decorator Receptacles, SF903R1 (Cutsheet)

## specifications

### General Info

- Color: Ivory
- Type: Receptacles
- Duty: Heavy Duty
- Special Features: Back,Side Wire
- Style: Decorator

## Listing Agencies/Third Party Information

- CSA Standard: Yes
- cUL Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406

## Dimensions

- Depth (U S): 0.833"
- Height U S: 3.281"
- Width U S: 1.322"

## Technical Information


- Amps: 20 Amp
- Volts: 125V
- Volts A C: 125
- Capacity: Duplex
- Grade Type: Specification

## Buy American Act Compliance


- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



## **resources** **BROCHURE**

 [Commercial & Industrial ProductsPDF \(3.52mb\)](#)

## **CUTSHEET**

 [Decorator Receptacles, SF903R1PDF \(364.17kb\)](#)